



Product Number: 8281

3M™ Dissipative Vinyl 3 Layer Floor Mat (Premium Performance)



Includes two 15 ft. (4.6 m) 3M Ground Cords 3040 and two 3M Snap Fasteners 3050 to be installed by user.

Note: 8230, 8240, 8270 and 8280 - no hardware included.

Additional Information:

3M Mats and Rolls 8200 Series are soft table and floor mats with a unique three-layer construction. The top layer is durable static dissipative vinyl, which has sufficiently low resistance to discharge static-laden conductors.

3M Id : 98-0798-1204-0

Characteristics:

Backing Material	Nonskid
Color	Brown
Construction	3-Layer
Dissipative	Yes
EPC Can View	Public
Hardness	65-70 Shore A
Length	40 Linear Foot
Material	Vinyl
Performance	Premium
Size	2 x 40 ft. (0.6 x 12.2 m)
Thickness	0.138 Inch
Type	Dissipative
Width	2 Linear Foot