



Product Number: COND48600FM

3M™ Floor Rolls 1864R

The 3M™ Floor Roll 1864R is a 50 ft. long roll of the mat material 1864. It includes two 15 ft. (4.6 m) 3M Ground Cords 3040 with 1 megohm resistor, five 3M Snap Fasteners 3034 and one 3M™ Snap Fastener Installation Tool.

Description:

Floor Roll 0.125 in. (3.2 mm) thick
 2 ft X 50 ft (0.6 m X 15.0 m)

Properties:

<u>Property</u>	<u>Typical Value</u>
Material	EVA Copolymer/Rubber
Thickness	0.125 in. (3.2 mm)
Hardness	80-85 Shore A
• Resistance	
(Surface to Ground)	9×10^2 ohm
(Surface to Surface)	6×10^2 ohm
* *Resistivity	10^2 ohm-cm

* Tested per ESD Association Standard S4.1 at 720 F, 50% RH using 3M Test Kit 701 for Static Control Surfaces (Megohmmeter).

**Tested per ASTM D 257