

Quick Reference

Search by part #

Check distributor part inventory

Products

Browse Products

-By Device -

-By Product Line-

-Attachment Methods

-Interface Materials -

-Accessories -

Useful Links

- [MSDS Safety Sheets](#)
- [How to Order?](#)
- [Find Sales Rep](#)
- [Find Distributor](#)
- [Sample Request](#)
- [Quote Request](#)
- [Catalog Request](#)
- [Building a Part #](#)
- [Part # Cross Ref](#)

Accessories

Standard Mounting Pads

The following Mounting Pads are for use with Integrated Circuits

<p>7717-21DAPG</p> <p>(DAP)</p> <p>Leads: 10</p> <p>Outside Diameter mm (in): 12.70 (0.500)</p> <p>Thickness: 6.99 (0.275)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-21NG</p> <p>(nylon)</p> <p>Leads: 10</p> <p>Outside Diameter mm (in): 12.70 (0.500)</p> <p>Thickness: 6.99 (0.275)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-19DAPG</p> <p>(DAP)</p> <p>Leads: 8</p> <p>Outside Diameter mm (in): 12.70 (0.500)</p> <p>Thickness: 6.99 (0.275)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-19NG</p> <p>(nylon)</p> <p>Leads: 8</p> <p>Outside Diameter mm (in): 12.70 (0.500)</p> <p>Thickness: 6.99 (0.275)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-107NG</p> <p>(nylon)</p> <p>Leads: 8</p> <p>Outside Diameter mm (in): 10.92 (0.430)</p> <p>Thickness: 3.30 (0.130)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-156DAPG</p> <p>(DAP)</p> <p>Leads: 14</p> <p>Outside Diameter mm (in): 19.05 x 11.43 (0.750 x 0.450)</p> <p>Thickness: 1.27 (0.050)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-156NG</p> <p>(nylon)</p> <p>Leads: 14</p> <p>Outside Diameter mm (in): 19.05 x 11.43 (0.750 x 0.450)</p> <p>Thickness: 1.27 (0.050)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-8DAPG</p> <p>(DAP)</p> <p>Leads: 8</p> <p>Outside Diameter mm (in): 9.53 (0.375)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-8NG</p> <p>(nylon)</p> <p>Leads: 8</p> <p>Outside Diameter mm (in): 9.53 (0.375)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-122DAPG</p> <p>(DAP)</p> <p>Leads: 8</p> <p>Outside Diameter mm (in): 9.27 (0.365)</p> <p>Thickness: 1.78 (0.070)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-122NG</p> <p>(nylon)</p> <p>Leads: 8</p> <p>Outside Diameter mm (in): 9.27 (0.365)</p> <p>Thickness: 1.78 (0.070)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-107DAPG</p> <p>(DAP)</p> <p>Leads: 8</p> <p>Outside Diameter mm (in): 10.92 (0.430)</p> <p>Thickness: 3.30 (0.130)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-30NG</p> <p>(nylon)</p> <p>Leads: 10</p> <p>Outside Diameter mm (in): 9.53 (0.375)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-30DAPG</p> <p>(DAP)</p> <p>Leads: 10</p> <p>Outside Diameter mm (in): 9.53 (0.375)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-6NG</p> <p>(nylon)</p> <p>Leads: 6</p> <p>Outside Diameter mm (in): 9.53 (0.375)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-6DAPG</p> <p>(DAP)</p> <p>Leads: 6</p> <p>Outside Diameter mm (in): 9.53 (0.375)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	