



Part Number: 7721-7PPSG

## **Insulating Shoulder Washers**

**RoHS Compliant** 

- 40% glass filled polyphenylene sulfide (PPS).
- Chemically inert [no known solvents under 200°C (392°F)]
- Maximum recommended service temperature of 260°C (500°F)
- Recommended torque is 0.565Nm to 0.678Nm (5 to 6 inch-pounds) on all shoulder washers except -7, which has recommended torque of 0.452Nm (4 inch-pounds).





## **Polyphenylene Sulfide PPS Shoulder Washers**

Note: A single gate extension, not to exceed 0.64mm (0.025") in length, is allowable on the outside of all shoulder washers.

Model	RoHS	Α	В	С	D	E	Screw Size	Fig.
7721-7PPSG*	RoHS ✓ Compliant	5.46 (0.215)	.81 (0.032)	1.02 (0.040)	2.95 (0.116)	3.43 (0.139)	4	1

• Design allows insertion in the tab of a TO-220.