





Rev	AWO #	Description	Date	Appr
-		RELEASED	04/14/05	

APPROVED: \_\_\_\_\_ TITLE: \_\_\_\_\_  
 DATE: \_\_\_\_\_



**SPECIFICATIONS:**

- Material:** Insulator: PBT, glass reinforced, rated UL 94V-0
- Insulator color: Black
- Contacts: Phosphor Bronze
- Plating:** Tin ver Copper underplate overall
- Electrical:** Operating voltage: 250 VAC max
- Current rating: 3 Amps max
- Contact resistance: 20 mohms max
- Insulation resistance: 5000 Mohms min
- Dielectric withstanding voltage: 1000 VAC for 1 minute
- Temperature Rating:** Operating temperature: -40C to +105C
- Environmental: Lead free, RoHS compliant.
- Recommended soldering temp: 230 for 5 sec.

A = .100 [2.54] X No. of Positions  
 B = .100 [2.54] X No. of Spaces

UNLESS OTHERWISE SPECIFIED	
ALL DIMENSIONS ARE INCHES [MM]	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	ØXX ± .10
.XX ± .020	ØXXX ± .015
.XXX ± .015	ØXXXX ± .010
APPROVALS	DATE
DRAWN	SS
CHECKED	
APPROVED	

**ADAM TECH**  
 909 Rahway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .100 RECEPTACLE STRIP, SINGLE ROW  
 STRAIGHT, PCB TAILS

SIZE	PART NO.	REV.
X	RS1-XX-T	-
REF:	SCALE: NTS	SHEET 1 OF 1



6

5

4

3

2

1