





Rev	AWO #	Description	Date	Appr
-		RELEASED	2/1/11	

APPROVED: _____
 DATE: _____ TITLE: _____



SPECIFICATIONS:

- Material: Nylon 66, rated UL 94V-2
- Insulator color: White
- Contacts: Brass
- Plating: Tin over Copper underplate overall
- Electrical:
 - Operating voltage: 250V AC,DC
 - Current rating: 7A AC,DC
 - Contact resistance: 10 mohms max
 - Insulation resistance: 1,000 Mohms min
 - Dielectric withstanding voltage: 1,500 VAC for 1 minute
- Temperature Rating:
 - Operating temperature: -25°C to +85°C
 - Temperature Rating: Anti-static plastic bags
- Environmental:
 - Anti-static plastic bags
- Lead free, RoHS compliant
- Recommended soldering temp: 235°C for 5 seconds



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .200 [5.08] POWER HEADER, STAIGHT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXXX ± .015
.XXX ± .015	ØXXX ± .010
APPROVALS	DATE
DRAWN AY	2/1/11
CHECKED AC	2/1/11
APPROVED	

SIZE X	PART NO. LHF-06-SA2-X02	REV. -
REF: S00099T	SCALE: NTS	SHEET 1 OF 1