

ADDA USA
DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
40 X 40 X 15	AD0412MX-D52	HYPRO	12	0.12	1.44	7000	8.1	0.210	31.8	27	2	UL,CUL,TUV,CE	500	44.00
40 X 40 X 15	AD0412HX-D50	HYPRO	12	0.12	1.44	8000	9.2	0.287	39.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412LB-D50	BALL	12	0.08	0.96	6000	6.8	0.161	30.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412LB-D50(S)	1B & 1S	12	0.08	0.96	6500	7.3	0.183	30.6	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412LB-D52	BALL	12	0.10	1.20	6000	6.8	0.161	30.3	27	2	UL,CUL,TUV,CE	500	44.00
40 X 40 X 15	AD0412MB-D50	BALL	12	0.10	1.20	7000	8.1	0.210	31.8	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412MB-D50(S)	1B & 1S	12	0.10	1.20	7500	8.5	0.231	33.5	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412MB-D52	BALL	12	0.12	1.44	7000	8.1	0.210	31.8	27	2	UL,CUL,TUV,CE	500	44.00
40 X 40 X 15	AD0412HB-D50	BALL	12	0.12	1.44	8000	9.2	0.287	39.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412HB-D50(S)	1B & 1S	12	0.12	1.44	8500	10.2	0.298	39.8	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412HB-D52	BALL	12	0.15	1.80	8000	9.2	0.287	39.3	27	2	UL,CUL,TUV,CE	500	44.00
40 X 40 X 15	AD0412HB-D56	BALL	12	0.12	1.44	8000	9.2	0.287	39.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412LS-D50	S	12	0.08	0.96	6000	6.8	0.161	30.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412MS-D50	S	12	0.10	1.20	7000	8.1	0.210	31.8	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412HS-D50	S	12	0.12	1.44	8000	9.2	0.287	39.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 20	AD0405LX-C50	HYPRO	5	0.14	0.70	5700	7.2	0.142	22.4	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405MX-C50	HYPRO	5	0.16	0.80	6300	7.8	0.171	26.3	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HX-C50	HYPRO	5	0.29	1.45	7500	9.2	0.250	31.0	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HX-C52	HYPRO	5	0.40	2.00	7500	9.2	0.250	31.0	28	2	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405DB-C50	BALL	5	0.12	0.60	4200	4.9	0.080	16.5	28	0,6	CE	500	36.96
40 X 40 X 20	AD0405LB-C50	BALL	5	0.14	0.70	6000	7.2	0.142	22.4	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405MB-C50	BALL	5	0.16	0.80	6500	8.1	0.171	27.0	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HB-C50	BALL	5	0.29	1.45	7800	9.9	0.256	31.9	28	0	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HB-C52	BALL	5	0.40	2.00	7800	9.9	0.256	31.9	28	2	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HB-C56	BALL	5	0.29	1.45	7800	9.9	0.256	31.9	28	6	CE	500	36.96
40 X 40 X 20	AD0405DS-C50	S	5	0.12	0.60	3700	4.7	0.064	10.0	28	0	CE	500	36.96
40 X 40 X 20	AD0405LS-C50	S	5	0.14	0.70	5700	7.2	0.142	22.4	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405MS-C50	S	5	0.16	0.80	6300	7.8	0.171	26.3	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HS-C50	S	5	0.29	1.45	7500	9.2	0.250	31.0	28	0	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HS-C56	S	5	0.29	1.45	7500	9.2	0.250	31.0	28	6	CE	500	36.96
40 X 40 X 20	AD0412DX-C50	HYPRO	12	0.05	0.60	3700	4.7	0.064	10.0	27	0,6	UL,CUL,CE	500	36.96
40 X 40 X 20	AD0412LX-C50	HYPRO	12	0.07	0.84	6000	7.5	0.154	23.9	27	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MX-C50	HYPRO	12	0.08	0.96	6700	8.3	0.180	27.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MX-C53	HYPRO	12	0.13	1.56	6700	8.3	0.180	27.5	28	3	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HX-C50	HYPRO	12	0.11	1.32	7500	9.6	0.240	31.0	27	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412DB-C50	BALL	12	0.05	0.60	4200	4.9	0.080	16.5	27	0	UL,CUL,CE	500	36.96
40 X 40 X 20	AD0412LB-C50	BALL	12	0.07	0.84	6200	7.7	0.165	25.0	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412LB-C51	BALL	12	0.11	1.32	6200	7.7	0.165	25.0	28	1,2	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MB-C50	BALL	12	0.08	0.96	6900	8.5	0.190	28.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MB-C52	BALL	12	0.13	1.56	6900	8.5	0.190	28.5	28	2,3	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HB-C50	BALL	12	0.10	1.20	7800	10.1	0.263	31.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HB-C52	BALL	12	0.15	1.80	7800	10.1	0.263	31.9	28	2	CE	500	36.96
40 X 40 X 20	AD0412HB-C53	BALL	12	0.15	1.80	7800	10.1	0.263	31.9	28	3	UL,CUL,TUV,CE	500	36.96

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED