

Features

- Android 6.1 operating system
- IPS HD screen
- CPU MTK6735 Quad core (A53 1.5-1.8GHZ)
- Capacitive multi-touch technology
- Resolution 1920x1200

AGDisplays

For over a decade AGDisplays has been a leading provider of high quality LCD enhancement products and services for the industrial markets. We provide a one stop shop with for LCD solutions. Our standard product offerings include a wide range of sizes, combinations that include NVIS, Coverglass, Touchscreen, High Bright LEDs, Bonding Services, Design Integration, Film Enhancements and more. We create new and enhancing existing designs, LCD ruggedization and simple or complex integration work. Our teams # 1 goal is to work hard to become your trusted partner.



SPECIFICATION

Model Number	AG101-A-F-4-2-IPNA-V1
Screen size	10.1 inch
Display type	IPS HD screen
Display resolution	1920x1200
Brightness (cd/m ²)	
WIFI	802.11 a/b/g/n
Memory (storage)	16GB/32GB
RAM (type/GB)	2GB DDR3
Operating system	Android 6.1
CPU	MTK6735 Quad core (A53 1.5-1.8GHZ)
GPU	N/A
Touchscreen	Capacitive multi touch
Camera	2MP/5MP
Bluetooth	Yes, 4.0
NFC	N/A
GPS	GPS
Operating temperature	

Storage temperature	
IP rating	N/A
Battery type	
Battery capacity	5000mAh
Battery run time (avg)	Video: about 4-5 hours
Product dimensions	240.2*170.2*9.2mm
Audio/video codec	
USB interface	High speed USB 2.0 micro USB
Headphone	Yes, 3.5mm
SIM card slot	1
HDMI port	No
Speaker	Dual Speaker
Sensors	G-sensor
Certifications	
Drop test	
Network	LTE CAT4/FDD-LTE/TD-LTE/WCDMA/TD-SCDMA/CDMA(1x-EVDO)/GSM GSM: 850/900/1800/1900MHz WCDMA: B1 (2100)/B5(850)/B8(900) EU FDD LTE: B1(2100)/B3(1800)/B7(2500)/B20(700) US FDD LTE:B2(1900)/B4(1700)/B7(2500)/B12(700) TD-SCDMA: B34/B39 TDD LTE: B40/B41 CDMA: 1X+EVDO
Expandable memory	Micro SD card, up to 32GB

Note: Specifications may be subject to change without prior notice.

