



Part Number: **N9340B-PA3**



DESCRIPTION:

The N9340B handheld RF spectrum analyzer provides powerful features for field applications, superior performance to build the confidence in field test, and exceptional usability to enhance field productivity.

Usability:

- 6.5" TFT color LCD for indoor and outdoor use
- 4-hour battery operating time
- Remote control via SCPI on USB and LAN* port
- Multi-language user interface: 11 languages
- One-button power measurement: Channel power, ACPR and OBW

Standard Features:

- Spectrogram
- Spectrum emission mask
- Agilent USB power sensor support
- Field strength measurement

Optional Features:

- AM/FM and ASK/FSK modulation analysis
- 3 GHz pre-amplifier
- 3 GHz tracking generator
- Hard transit case
- Automotive 12 DC adaptor
-

KEY SPECIFICATIONS:

- 100 kHz to 3 GHz frequency range
- 10 ms non-zero span sweep time
- 30 Hz to 1 MHz RBW in 1-3-10 sequence
- -144 dBm displayed average noise level (DANL) with pre-amplifier
- +10 dBm third order intercept (TOI)