

You have not login, do you need to [Login](#) or [Register?](#)

Series [D_DF](#) [D-ST](#) [DFR](#) [ED_EHD](#) [EF](#) [H](#) [HD](#) [HTH](#) [HTN](#) [MP](#) [RR_HR_Housing](#) [RR_HR_Contacts](#) [SD](#) [SM](#) [TF](#) [TS](#) [TW](#)
[TW_CNTS](#) [Home](#)

TW [Hide Search](#) [All Records](#) [Back To Series](#)

Search: Part Number

Termination Gender Footprint Style Shell / Plating
 Contact Plating Footprint Dimensions With / Without Boardlocks Panel Mounting Option
 Board Mounting Options - Straight

Part Number	Termination	Gender	Footprint Style	Shell / Plating	Contact Plating	Footprint Dimensions P=Power, C=Coax, S=Signal	With / Without Boardlocks	Panel Mounting Option	Board Mounting Options - Straight	Customer Drawing
L177TWA7W2SHP2SV4RRM6	Power (20A) & Signal Contacts	Socket	Right Angle PCB Mount Mixed Footprint	Bright Tin	0.76µm (30µin) Power & 0.76µm (30µin) Signal	P=11.57mm (.456in) S=10.30mm (.406in)	With Boardlocks	4-40 Rear Threaded Screwlock		-

Total 1 Records. Page:1/1 Home - [Prev](#) - [Next](#) - [Last](#) Jump:

Copyright© 2006-2007 Amphenol China All rights reserved