


NOTES:

1. COMPONENTS:
  - CONNECTOR: MUSB-A111-X0, RECEPTACLE, TYPE A, SINGLE, 4 CONTACTS PER PORT.
  - USB TERMINATION: USB, RECEPTACLE, TYPE A, SINGLE, 4 CONTACTS PER PORT.
2. FEATURE: SEALED CONNECTOR IN THE MATED AND UNMATED CONDITIONS.
3. OPERATING TEMPERATURE: -40°C TO +105°C.
4. ENVIROMENT PERFORMANCE: IP67.
5. ALL COMPONENTS AND MATERIALS USED FOR CONNECTOR AND PACKAGING ARE ROHS COMPLIANT PER EU DIRECTIVE 2002/95/EC AND AMENDMENTS.


UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER TOLERANCES ARE:  DECIMALS                      ANGLES .XX ± .10                      ± 1° .X ± .25	APPROVALS	DATE	<b>Amphenol Canada Corp.</b>		
	DRAWN S.SEMENOV	JAN15/06			
	DESIGNED S.SEMENOV	JAN15/06	TITLE <b>USB CONNECTOR, TYPE A, SINGLE, WITH USB TERMINATION</b>		
	CHECKED				
	MATERIAL AND FINISH	QA APP'D		SIZE C	DWG. NO. P-MUSB-A311-30
REF.	IE APP'D		SCALE 2.5:1	PROJECT MUSB	SHEET 1 OF 2
CODE IDENT. NO.	DWG APP'D A.GREEN	JAN15/06			

DO NOT SCALE DRAWING  
THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.

REV	DESCRPT	DATE	APPRVD



RECOMMENDED PANEL CUTOUT



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER TOLERANCES ARE:		APPROVALS	DATE	<b>Amphenol Canada Corp.</b>		
		DRAWN S.SEMENOV	JAN15/06			
DECIMALS .XX ± .10 .X ± .25	ANGLES ± 1°	DESIGNED S.SEMENOV	JAN15/06	TITLE <b>USB CONNECTOR, TYPE A, SINGLE, WITH USB TERMINATION</b>		
		CHECKED				
MATERIAL AND FINISH		QA APP'D				
REF.		IE APP'D		SCALE 2.5:1		PROJECT MUSB
CODE IDENT. NO.		DWG APP'D A.GREEN	JAN15/06	SHEET 2 OF 2		

DO NOT SCALE DRAWING  
THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.