





	1	2	3	4	5	6	7																																																																																	
A	   Electrical test: 1. 100% short, open, miss wire test 2. Conduct resistance: 2 Ohm(max) 3. Insulation resistance: 5Mohm(min) 4. Dielectric test: DC 300V																																																																																							
B																																																																																								
C																																																																																								
D																																																																																								
E																																																																																								
F	 PIN ASSIGNMENT: <table><thead><tr><th>P1</th><th>P2</th></tr></thead><tbody><tr><td>1</td><td>8</td></tr><tr><td>2</td><td>3</td></tr><tr><td>3</td><td>2</td></tr><tr><td>4</td><td>20</td></tr><tr><td>5</td><td>7</td></tr><tr><td>6</td><td>6</td></tr><tr><td>7</td><td>4</td></tr><tr><td>8</td><td>5</td></tr><tr><td>9</td><td>22</td></tr><tr><td>SHELL</td><td>SHELL</td></tr></tbody></table> <table><thead><tr><th>NO.</th><th>NAME</th><th>QTY</th><th>SPECIFICATION</th></tr></thead><tbody><tr><td>⑨</td><td>PE BAG</td><td>1/10</td><td>CLEAR SIZE: 170*250*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"</td></tr><tr><td>⑧</td><td>PE BAG</td><td>1</td><td>CLEAR SIZE: 80*100*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"</td></tr><tr><td>⑦</td><td>NUT</td><td>2</td><td>UNT:#4-40UNC 4.75*5.9mm NICKEL PLATED</td></tr><tr><td>⑥</td><td>SCREW</td><td>4</td><td>THUMB SCERW #4-40UNC L21mm MOLD BEIGE(IV-29#)</td></tr><tr><td>⑤</td><td>OUT JACKET</td><td>30g</td><td>40P PVC BEIGE(IV-29#)</td></tr><tr><td>④</td><td>IN JACKET</td><td>7.8g</td><td>CLEAR LD-PE</td></tr><tr><td>③</td><td>CABLE</td><td>445mm</td><td>UL 1007 26AWG COLOR BLACK L1=45mm*9PCS L2=50mm*1PCS.</td></tr><tr><td>②</td><td>CONN</td><td>1</td><td>DB25P FEMALE SOLDER TYPE PIN G/F, BLUE INSULATION SHELL-NICKEL,</td></tr><tr><td>①</td><td>CONN</td><td>1</td><td>DB9P MALE SOLDER TYPE G/F, BLUE INSULATION SHELL-NICKEL,</td></tr></tbody></table> 1PC/PE BAG							P1	P2	1	8	2	3	3	2	4	20	5	7	6	6	7	4	8	5	9	22	SHELL	SHELL	NO.	NAME	QTY	SPECIFICATION	⑨	PE BAG	1/10	CLEAR SIZE: 170*250*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"	⑧	PE BAG	1	CLEAR SIZE: 80*100*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"	⑦	NUT	2	UNT:#4-40UNC 4.75*5.9mm NICKEL PLATED	⑥	SCREW	4	THUMB SCERW #4-40UNC L21mm MOLD BEIGE(IV-29#)	⑤	OUT JACKET	30g	40P PVC BEIGE(IV-29#)	④	IN JACKET	7.8g	CLEAR LD-PE	③	CABLE	445mm	UL 1007 26AWG COLOR BLACK L1=45mm*9PCS L2=50mm*1PCS.	②	CONN	1	DB25P FEMALE SOLDER TYPE PIN G/F, BLUE INSULATION SHELL-NICKEL,	①	CONN	1	DB9P MALE SOLDER TYPE G/F, BLUE INSULATION SHELL-NICKEL,																			
P1	P2																																																																																							
1	8																																																																																							
2	3																																																																																							
3	2																																																																																							
4	20																																																																																							
5	7																																																																																							
6	6																																																																																							
7	4																																																																																							
8	5																																																																																							
9	22																																																																																							
SHELL	SHELL																																																																																							
NO.	NAME	QTY	SPECIFICATION																																																																																					
⑨	PE BAG	1/10	CLEAR SIZE: 170*250*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"																																																																																					
⑧	PE BAG	1	CLEAR SIZE: 80*100*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"																																																																																					
⑦	NUT	2	UNT:#4-40UNC 4.75*5.9mm NICKEL PLATED																																																																																					
⑥	SCREW	4	THUMB SCERW #4-40UNC L21mm MOLD BEIGE(IV-29#)																																																																																					
⑤	OUT JACKET	30g	40P PVC BEIGE(IV-29#)																																																																																					
④	IN JACKET	7.8g	CLEAR LD-PE																																																																																					
③	CABLE	445mm	UL 1007 26AWG COLOR BLACK L1=45mm*9PCS L2=50mm*1PCS.																																																																																					
②	CONN	1	DB25P FEMALE SOLDER TYPE PIN G/F, BLUE INSULATION SHELL-NICKEL,																																																																																					
①	CONN	1	DB9P MALE SOLDER TYPE G/F, BLUE INSULATION SHELL-NICKEL,																																																																																					
G	RoHS compliant Unit: mm <table><thead><tr><th>Scale</th><th>Free</th><th></th><th></th><th></th><th></th><th></th><th></th></tr></thead><tbody><tr><td colspan="2">TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td></td><td></td></tr><tr><td></td><td></td><td>⑩</td><td>Drawn</td><td>20.02.2017</td><td>Amy</td><td></td><td></td></tr></tbody></table> ASSMANN components Drawing-No. ASS 7870 CA rev00 Customer-No. ASSMANN WSW-No. AB914F							Scale	Free							TOLERANCE																																DIM	TOL																							Angle	TOL	Id.	Modification	Date	Name					⑩	Drawn	20.02.2017	Amy			
Scale	Free																																																																																							
TOLERANCE																																																																																								
DIM	TOL																																																																																							
Angle	TOL	Id.	Modification	Date	Name																																																																																			
		⑩	Drawn	20.02.2017	Amy																																																																																			
H	<table><thead><tr><th>1</th><th>2</th><th>3</th><th>4</th><th>5</th><th>6</th><th>7</th></tr></thead><tbody><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr></tbody></table>							1	2	3	4	5	6	7																																																																										
1	2	3	4	5	6	7																																																																																		