




A | B | C | D | E | F

IDC10P,W/SR & NOSE

DB9 MALE



CONFIGURATION:
IDC10P DB9M



MAT'L:
 1.CABLE:FLAT CABLE,UL2651,#28,9C,GRAY,1.27mm PITCH
 RED LINE PIN1
 2.CONNECTOR:DB9M,INSULATION IS BLACK,SOLDER TYPE
 IDC 10P,W/NOSE,BLACK COLOR,2.54mm PITCH

NOTE;
 1.TOTAL LENGTH:300±20mm



6/6,05'	01	Item no. change	
DATE	REVISION	MODIFY DISCRPTION	
DATE	9 APR,2001	ITEM NO	A-TA3237-R
UNIT	MM	ORDER NO	CS05-0384
SCALE	NTS	BUYER NO	002

TITLE: IDC 10PIN SOCKET-DB9 MALE
A-TA3237-R

DRAWN	CHECK	APPRO
-------	-------	-------