





Rev	AWO #	Description	Date	Appr
-		RELEASED	8/9/11	

APPROVED: _____
 DATE: _____ TITLE: _____



PACKAGED ON TAPE & REEL
 Positions: 2 thru 16
 A = .079 [2.00] x No. of Positions + .153 [3.90]
 B = .079 [2.00] x No. of Spaces
 C = .079 [2.00] x No. of Positions + .024 [0.60]

SPECIFICATIONS:
 Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
 Insulator color: Natural
 Contacts: Brass
 Plating: Tin over Copper underplate overall
 Electrical: Operating voltage: 100 VAC max
 Current rating: 2 Amps max
 Contact resistance: 10 mohms max
 Insulation resistance: 1,000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 800 VAC for 1 minute
 Temperature Rating: Operating temperature: -25°C to +85°C
 Environmental: Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .079 [2.00] SHRROUDED HEADER, WITH CAP
 VERTICAL, SURFACE MOUNT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM]		TOLERANCES: EXCEPT AS NOTED	
INCHES		HOLDS	
.X	± .10	ØXX	± .10
.XX	± .020	ØXXX	± .015
.XXX	± .015	ØXXXX	± .010
APPROVALS		DATE	
DRAWN	AY	8/5/11	
CHECKED	CC	8/9/11	
APPROVED			
SIZE	PART NO.	REV.	
X	2SH-C-XX-TS-SMT-PP-1/R	-	
REF:	S00015T	SCALE:	NTS
SHEET 1 OF 2		SHEET 1 OF 2	