







APPROVED: _____
DATE: _____ TITLE: _____




SPECIFICATIONS:

Material: Insulator: PBT, Glass reinforced, rated UL 94V-0
Insulator color: Black
Center Pin: Brass, Nickel plated
Contacts: Copper Alloy
Plating: Silver over Nickel underplate

Electrical: Operating voltage: 20 VDC max.
Current rating: 3 Amp max.
Contact resistance: 30 mohms max. initial
Insulation resistance: 100 Mohms min.
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating: Operating temperature: -20°C to +70°C
Environmental: Lead free, RoHS compliant



Rev	AWO #	Description	Date	Appr
-		RELEASED	12/10/04	
A		REDESIGNED	8/2/06	
B		UPDATED & CORRECTED DIMENSIONS	11/03/06	
C		REVISED CURRENT RATING	3/20/09	
D		REDRAWN	1/17/12	
E		REVISED DIM.	5/31/12	



PART NO.	CENTER PIN DIA.
ADC-010-1	.079 [2.00]
ADC-010-2	.098 [2.50]
ADC-010-5	.092 [2.35]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

DC POWER JACK

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES Holes				DATE			
.X	± .10	ØXX	± .10	.X	± .10	ØXX	± .10
.XX	± .020	ØXX	± .015	.XX	± .015	ØXX	± .010
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	SS	10/4/04					
CHECKED							
APPROVED							
TITLE				REV.			
DC POWER JACK				E			
SIZE PART NO. ADC-010-X							
REF: S0002C							
SCALE: NTS							