





APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

| Rev | AWO # | Description | Date    | Appr |
|-----|-------|-------------|---------|------|
| -   |       | RELEASED    | 9/05/08 |      |
| A   |       | ADDED SPEC. | 7/25/11 |      |



Recommended PCB Layout



#### SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Natural

Contacts: Brass, Tin plated

Electrical:

Voltage rating: 600 V

Current rating: 2~4P: 13A, 6~10P: 11A

Dielectric withstanding voltage: 5000 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Poles: 02 thru 10

A = .250 [6.35] X No. of Positions + .050 [1.27]

B = .250 [6.35] X No. of Spaces

UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE MM [INCHES]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES  
.X ± .10 Ø.X ± .10  
.XX ± .020 Ø.XX ± .015  
.XXX ± .015 Ø.XXX ± .010

| APPROVALS |    | DATE    |
|-----------|----|---------|
| DRAWN     | DY | 9/05/08 |
| CHECKED   |    |         |
| APPROVED  |    |         |

## ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE WIRE TO BOARD, FEMALE, 6.35mm PITCH  
WITHOUT POLARIZING, SINGLE ROW TYPE

|               |                           |              |
|---------------|---------------------------|--------------|
| SIZE<br>X     | PART NO.<br>DME-XX-S-S-V0 | REV.<br>A    |
| REF: S000123T | SCALE: NTS                | SHEET 1 OF 1 |