





Rev	AWO #	Description	Date	Appr
-		RELEASED	10/27/10	

APPROVED: _____
 DATE: _____ TITLE: _____



A-A SECTION



B-B SECTION

PART #	WIRE AWG	DIMENSIONS			
		a	b	c	d
DME-A-C-F-R	18 ~ 22	.094 [2.40]	.094 [2.40]	.134 [3.40]	.134 [3.40]
DME-B-C-F-R	16 ~ 20	.114 [2.90]	.138 [3.50]	.177 [4.50]	.173 [4.40]
DME-C-C-F-R	12 ~ 14	.126 [3.20]	.165 [4.20]	.252 [6.40]	.224 [5.70]

SPECIFICATIONS:
 Material: Brass
 Contacts: Brass
 Thickness: 0.3mm
 Plating:
 Tin over Copper underplate overall
 Electrical:
 Voltage rating: 600V
 Current rating: 13A
 Temperature Rating:
 Operating temperature: -55°C to +105°C
 Environmental:
 Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: CRIMP CONTACT, DME SERIES, FEMALE
 TIN PLATED, ON REELS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		DRAWN: DY		DATE: 10/27/10	
INCHES .X ± .10 .XX ± .020 .XXX ± .015		HOLDS ØX ± .10 ØXX ± .015 ØXXX ± .010		APPROVALS	
CHECKED		SIZE	PART NO.	REV.	
APPROVED		X	DME-X-C-F-R		
		REF: S00123T	SCALE: NTS	SHEET 1 OF 1	