






Rev	AWO #	Description	Date	Appr
-		RELEASED	11/22/10	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PANEL HOLE

SPECIFICATIONS:

Material:

Insulator: Thermoplastic, rated UL94V-2

Insulator color: Natural

Contact: Copper Alloy

Electrical:

Current rating: 13A

Voltage rating: 600V

Insulation resistance: 1,000 Mohms min.

Withstand voltage: 5000V AC/ minute

Temperature range: -55°C to +105°C

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

.250 [6.35] WIRE TO WIRE, FEMALE, 4 POLES

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES	HOLES						
.X ± .10	ØX ± .10						
.XX ± .020	ØXX ± .015						
.XXX ± .015	ØXXX ± .010						
APPROVALS				DATE			
DRAWN	DY			11/22/10			
CHECKED							
APPROVED							
SIZE	PART NO.						
X	DME-F-04						
REF:	S00004T	SCALE:	NTS	SHEET	1	OF	1