

6

5

4

3





2

1


| Rev | AWO # | Description | Date     | Appr |
|-----|-------|-------------|----------|------|
| -   |       | RELEASED    | 11/22/10 |      |

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



RECOMMENDED PANEL HOLE



**SPECIFICATIONS:**

**Material:**

Insulator: Thermoplastic, rated UL94V-2

Insulator color: Natural

Contact: Copper Alloy

**Electrical:**

Current rating: 13A

Voltage rating: 600V

Insulation resistance: 1,000 Mohms min.

Withstand voltage: 5000V AC/ minute

Temperature range: -55°C to +105°C

**Environmental:**

Lead free, RoHS compliant.



**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .250 [6.35] WIRE TO WIRE, MALE, 4 POLES

SIZE: PART NO. DME-M-04 REV. -

CHECKED: APPROVED: REF: S00004T SCALE: NTS SHEET 1 OF 1

A

B

C

D

A

B

C

D

6

5

4

3

2

1