




Rev	AWO #	Description	Date	Appr
-		RELEASED	11/9/06	

APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



**SPECIFICATIONS:**

Material: Insulator: Nylon 66, rated UL 94V-0  
 Insulator color: Black  
 Electrical: Operating voltage: 250 VAC RMS max  
 Current rating: 20 Awg: 5 Amps max  
 22 Awg: 5 Amps max  
 24 Awg: 4 Amps max  
 26 Awg: 3 Amps max  
 28 Awg: 2 Amps max  
 30 Awg: 1 Amp max.

Insulation resistance: 1000 Mohms min @ 500 VDC  
 Dielectric withstanding voltage: 1500 VAC for 1 minute

Mechanical: Wire size: 20 Awg thru 30 Awg  
 Temperature Rating: Operating temperature: -25°C to +120°C  
 Environmental: Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES]	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXXX ± .015
.XXX ± .015	ØXXX ± .010
APPROVALS	DATE
DRAWN	SS
CHECKED	1/19/06
APPROVED	

**ADAM TECH**  
 909 Rahway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .118" [3.0mm] CRIMP HOUSING, SINGLE ROW  
 LATCHING TYPE

SIZE	PART NO.	REV.
X	DMT-1-2	-
REF:	SCALE: NTS	SHEET 1 OF 1