








Rev	AWO #	Description	Date	Appr
-		RELEASED	5/27/08	

APPROVED: _____
 DATE: _____ TITLE: _____



Recommended
PCB Layout



PACKAGED ON TAPE AND REEL

SPECIFICATIONS:

- Material: Insulator: Hi-Temp Nylon PA6T, rated UL 94V-0
- Insulator color: Black
- Contactors: Copper Alloy
- Shell: Stainless Steel, Nickel over plated
- Plating: Gold Flash over Nickel overall
- Electrical:
 - Operating voltage: 30 VAC max.
 - Current rating: 1 Amp max.
 - Contact resistance: 50 mohms max.
 - Insulation resistance: 100 Mohms min. @ 500 VDC
 - Dielectric withstanding voltage: 250 VAC for 1 minute
- Temperature Rating:
 - Operating temperature: -55°C to +105°C
- Environmental:
 - Lead free, RoHS compliant.
 - Recommended soldering temp: 260°C for 5 sec.

ADAM TECH

909 Railway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: MICRO USB, TYPE B, SINGLE PORT
 RIGHT ANGLE, SMT, TAPE AND REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
X.XX ± .10	ØXX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010
APPROVALS	DATE
DRAWN SS	5/27/08
CHECKED	
APPROVED	

SIZE	PART NO.	REV.
X	MCR-B-S-RA-TSMT-TR	-
REF:	SCALE: NTS	SHEET 1 OF 1