



| Rev | AWO # | Description | Date | Appr |
|-----|-------|-------------|----------|------|
| - | | RELEASED | 12/30/05 | |

APPROVED: _____ TITLE: _____
 DATE: _____



MATING FACE CONFIGURATIONS

| MDJ-003-FS-PUR | MDJ-004-FS-PUR | MDJ-005-FS-PUR | MDJ-006-FS-PUR | MDJ-007-FS-PUR | MDJ-008-FS-PUR |
|----------------|----------------|----------------|----------------|----------------|----------------|
| | | | | | |

SPECIFICATIONS:

Material: Insulator color: Purple, Pantone color 2715C
 Insulator: PBT, glass filled, rated UL 94V-0
 Contacts: Phosphor Bronze
 Shield: Copper Alloy, Tin plated
 Plating: Gold over Nickel underplate on contact area, Tin over Copper underplate on tails

Electrical:

Operating voltage: 100 VAC/12 VDC max.
 Current rating: 1 Amp max./2 Amps max.
 Contact resistance: 30 mohms max. initial
 Insulation resistance: 100 Mohms min.
 Dielectric withstanding voltage: 250 VAC for 1 minute
 Temperature Rating: Operating temperature: -25°C to +70°C
 Environmental: Lead free, RoHS compliant.
 Recommended soldering temp: 235 for 5 sec.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: MINI DIN JACK, RIGHT ANGLE, FULL SHIELD
 PURPLE, PANTONE COLOR 2715C

| | | | | | |
|---|--------|------------|--------|----------------|--------|
| UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED | | INCHES | | HOLES | |
| X | ± .10 | ØXX | ± .10 | ØXXX | ± .015 |
| .XX | ± .020 | ØXXX | ± .015 | ØXXX | ± .010 |
| XXX | ± .015 | ØXXX | ± .010 | ØXXX | ± .010 |
| APPROVALS | | DATE | | TITLE | |
| DRAWN | SS | 12/30/05 | | SIZE | |
| CHECKED | | | | PART NO. | |
| APPROVED | | | | MDJ-00X-FS-PUR | |
| REF: | | SCALE: NTS | | SHEET 1 OF 1 | |