






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/28/04	
A		REDRAWN	5/03/11	



SPECIFICATIONS:

Material:

Housing: PBT, glass reinforced

Contact terminal: Phosphor Bronze, silver plated

Ground terminal: Brass, Tin plated

Electrical:

Operating voltage: 100V AC 1A MAX or 12V DC 2A MAX

Contact resistance: 30 mohms max.

Insulation resistance: 100 Mohms min @ 500V DC

Dielectric withstanding voltage: 250 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MINI DIN JACK, VERTICAL TYPE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
HOLES							
.X	± .10	ØX	± .10				
.XX	± .020	ØXX	± .015				
.XXX	± .015	ØXXX	± .010				
APPROVALS		DATE		MINI DIN JACK, VERTICAL TYPE			
DRAWN	SS	6/28/04					
CHECKED							
APPROVED							
REF: S00095T	SIZE	PART NO.	MDV-004	SCALE: NTS	SHEET 1 OF 1	REV. A	