




Rev	AWO #	Description	Date	Appr
-		RELEASED	8/31/10	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max.

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 800 VAC for 1 minute

Mechanical:

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.

Recommended soldering temp: 235°C for 5 sec.



Poles: 6 thru 72
A = .100 [2.54] X No. of Spaces + .281 [7.14]
B = .100 [2.54] X No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED

.X ± .10 ØXX ± .10
.XX ± .020 ØXXX ± .015
.XXX ± .015 ØXXXX ± .010

TITLE

.100 [2.54] CRIMP TERMINAL HOUSING

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

ADAM TECH

APPROVALS	DATE	SIZE	PART NO.	REV.
DRAWN	DY	8/31/10	MTFA-XX	-
CHECKED				
APPROVED				