



AWG	mm ²	L ₂		Industry Standard color	Cat. No.	DIN Standard color	Cat. No.	Dimensions (mm)						Std.* Pack
		Barrel Length (mm)						L ₁	L ₂	D ₁	S ₂	D ₂	S ₂	
26	0.14	6		grey	● FII2606M			10	6	0.6	0.15	1.5	0.25	100
26	0.14	8		grey	● FII2608M			12	8	0.6	0.15	1.5	0.25	100
24	0.25	6		light blue	● FII2406M			10	6	0.85	0.15	1.8	0.25	100
24	0.25	8		light blue	● FII2408M			12	8	0.85	0.15	1.8	0.25	100
24	0.25	12		light blue	● FII2412M			16	12	0.85	0.15	1.8	0.25	100
22	0.34	6		turquoise	● FII2206M			10	6	0.85	0.15	2	0.25	100
22	0.34	8		turquoise	● FII2208M			12	8	0.85	0.15	2	0.25	100
22	0.34	12		turquoise	● FII2212M			16	12	0.85	0.15	2	0.25	100
20	0.5	6		orange	● FII2006M	white ○ FID2006M		12	6	1	0.15	2.6	0.25	100
20	0.5	8		orange	● FII2008M	white ○ FID2008M		14	8	1	0.15	2.6	0.25	100
20	0.5	10		orange	● FII2010M	white ○ FID2010M		16	10	1	0.15	2.6	0.25	100
20	0.5	12		orange	● FII2012M	white ○ FID2012M		18	12	1	0.15	2.6	0.25	100
18	0.75	6		white	○ FII1806WM	grey ● FID1806GRM		12	6	1.2	0.15	2.8	0.25	100
18	0.75	8		white	○ FII1808WM	grey ● FID1808GRM		14	8	1.2	0.15	2.8	0.25	100
18	0.75	10		white	○ FII1810WM	grey ● FID1810GRM		16	10	1.2	0.15	2.8	0.25	100
18	0.75	12		white	○ FII1812WM	grey ● FID1812GRM		18	12	1.2	0.15	2.8	0.25	100
18	1	6		yellow	● FII1806YM	red ● FID1806RM		12	6	1.4	0.15	3	0.25	100
18	1	8		yellow	● FII1808YM	red ● FID1808RM		14	8	1.4	0.15	3	0.25	100
18	1	10		yellow	● FII1810YM	red ● FID1810RM		16	10	1.4	0.15	3	0.25	100
18	1	12		yellow	● FII1812YM	red ● FID1812RM		18	12	1.4	0.15	3	0.25	100
16	1.5	6		red	● FII1606M	black ● FID1606M		12	6	1.7	0.15	3.5	0.25	100
16	1.5	8		red	● FII1608M	black ● FID1608M		14	8	1.7	0.15	3.5	0.25	100
16	1.5	10		red	● FII1610M	black ● FID1610M		16	10	1.7	0.15	3.5	0.25	100
16	1.5	12		red	● FII1612M	black ● FID1612M		18	12	1.7	0.15	3.5	0.25	100
14	2.08	8		yellow	● FII1408YM			15	8	2.05	0.15	4.2	0.25	100
14	2.5	6		blue	● FID1406M			13	6	2.2	0.15	4.2	0.25	100
14	2.5	8		blue	● FID1408M			15	8	2.2	0.15	4.2	0.25	100
14	2.5	10		blue	● FID1410M			17	10	2.2	0.15	4.2	0.25	100
14	2.5	12		blue	● FID1412M			19	12	2.2	0.15	4.8	0.25	100
12	4	8		grey	● FID1208M			16	8	2.8	0.2	4.8	0.3	50
12	4	10		grey	● FID1210M			18	10	2.8	0.2	4.8	0.3	50
10	6	12		black	● FII1012M	yellow ● FID1012M		20	12	3.5	0.2	6.3	0.3	20
8	10	12		ivory	● FII0812M	red ● FID0812M		22	12	4.5	0.2	7.6	0.4	20

For Larger Packs see page 4.