

NOW Available

Enclosed Manual Motor Controllers

(25 - 150A/600V) in NEMA Type 4X



AC Motor across-the-line
AC General use

Altech's controllers can be used locally at the motor.



Type/Cat. #		Ampere Rating		Poles*	208V	415V	480V	600V	Wire Size Cu only
Black Pistol Handle	Yellow/Red Pistol Handle								
KEM325L	KEM325LY/R	25A/600V	3P	5HP	10HP	15HP	10HP	14-8 AWG	
KEM340L	KEM340LY/R	40A/600V	3P	7.5HP	15HP	20HP	15HP	14-8 AWG	
KEM360L	KEM360LY/R	60A/600V	3P	10HP	20HP	25HP	25HP	12-4 AWG	
KEM380L	KEM380LY/R	80A/600V	3P	15HP	25HP	30HP	40HP	4-1/0 AWG	
KEM3100L	KEM3100LY/R	100A/600V	3P	15HP	30HP	40HP	50HP	4-1/0AWG	
KEM3125L	KEM3125LY/R	125A/600V	3P	20HP	40HP	50HP	60HP	4-1/0 AWG	
KEM3150L	KEM3150LY/R	150A/600V	3P	25HP	50HP	60HP	75HP	4-1/0AWG	

DOOR INTERLOCK HANDLES



Type/Cat. #	Type/Cat. #	Color
LK3/OK2	LK11 U	Black
LK2/OK2	LK11 Y/R U	Yellow/Red

AUXILIARY SWITCHES



Electrical Rating:
10A/ 1/2HP 125-250 VAC

Type/Cat. #	Type/Cat. #	For Use With
1NO/1NC	2NO/2NC	
KU1.V	KU2.V	KU models
VKA1.V	VKA2.V	VKA models

DOOR INTERLOCK SHAFTS (STEEL)



Type/Cat. #	Length (L)
L100AD11-ST	100mm
L200AD11-ST	200mm
L300AD11-ST	300mm

DIRECT HANDLE



Type/Cat. #	Type/Cat. #	For Use With
K/KU3P	K/KU3P Y/R	KU325/340/363
K/KU4P	K/KU4P Y/R	KU425/440/463
K/KU3-4P	K/KU3-4P Y/R	VKA Models

DOOR MOUNTING KIT Small Body

Shown with Display Bracket



Type/Cat. #	Selector Handle Color	For Use With
OKA 0.V	Black	KU Direct
OKA 0.V Y/R	Yellow/Red	Handle Models

COVER PLATE FOR TOGGLE TYPE



Cover Type	Grey	Yellow
Rectangular	K/KUE	K/KUE Y
Circular	R/KUE	R/KUE Y

DOOR MOUNTING KIT Large Body



Type/Cat. #	Pistol Handle Color	For Use With
OKA/V LK11	Black	VKA Direct
OKA/V LK11 Y/R	Yellow/Red	Handle Models

FUSE HOLDER**



Shown with Extended Handle Switch

Type/Cat. #	Electrical Rating
KV10x38CC	30A/600V
KV10x38	30A/600V

For midget and CC-fuses.

* 4 pole versions available on all models.

** Use only with 40A extended handle switch (Type/Cat. # KU340N)