



PIN	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
COM	COM				1E	1D	1C	1DP	2E	2D	2C	2DP	3E	3D	3C	3DP	4E	4D	4C	4B
PIN	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
COM	4A	4F	4G	3B	3A	3F	3G	□	2B	2A	2F	2G		1B	1A	1F	1G	△		COM

NOTES:

- VIEWING ANGLE: 6:00 O' CLOCK
- DISPLAY MODE: POSITIVE/TRANSMISSIVE/TN TYPE
- DRIVING VOLTAGE: 3.0-5.0V, STATIC
- OPERATING TEMP.: -30 TO 85
- STORAGE TEMP.: -40 TO 90
- CONNECTOR: PIN TYPE

6					AZ Displays					
5					PART NO. GD-042FWP					
4					DESIGN BY					
3					CHECKED BY					
2					APP BY					
1	MODIFY DISPLAY MODE	2003.1.24	L. J. Q		TOLERANCES UNLESS OTHERWISE STATED X .20 XX .10 ALL DIMENSIONS IN MM UNLESS OTHERWISE STATED					
VER.	MODIFY CONTENTS	DATE	DESIGN		SHEET 1 OF 1					