






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C190323	2019/03/04	Vicky	Change Note




Recommended Panel
Cut-Out





AAD-XXPMMS-LC7001

02:2Pin
03:3Pin



Note:

- * **QC** Important Dimension To Check.
- * Waterproof Rate: IP67, Unmated.
- * Housing: Thermoplastic, Black.
- * Pin: Copper Alloy, Gold Plated.
- * Nut: Thermoplastic, Black.
- * Gasket: Rubber, Gray.
- * Use with waterproof cap or dust cap
Maximum Panel Thickness: 2.3mm
- * Use without waterproof cap or dust cap
Maximum Panel Thickness: 3.5mm
- * Gasket and Nut are packed separately in PE bags.
(Gasket/Nut不組裝, 散裝出貨)



3 Pin
2 Pin
Pin Assignments Front View

UNIT:mm			TITLE			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY		DATE		
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°			MINI PANEL SCREW M CONN M PIN					DWG NO		CHECKED BY		DATE		
			SCALE 2:1			SIZE A4			AAD-XXPMMS-LC7001		Rita		2019-03-04	
			SHEET 1 OF 1			QC: Inspection item		CUSTOMER		APPROVED BY		DATE		
			REV. B					WC-REV. A.3		ALTW		Max		2019-03-04