REV.	ECN NO.	DATE	SIGN	DESCRIPTION
D	LEN-8B0339	2008/09/19	Shin	Add Note
E	LEN1730300	2017/03/21	Ruru	Change Logo
F	C190273	2019/02/25	Ruru	Modify Note

ALTW
CONFIDENTIAL
2019-02-25
R&D DEPT.

Note: E F
* QC Important Dimension To Check.
* Waterproof Rate: IP67, Unmated
* Housing: Thermoplastic, Black
* Pin: Copper Alloy, Gold Plated
* Nut: Thermoplastic, Black
* Gasket: Rubber, Black
D * Liquid Glue:Black
* Use With Waterproof Cap Or Dust Cap
D Panel Thickness Max: 3.0mm
* Use Without Waterproof Cap Or Dust Cap
Panel Thickness Max: 4.5mm
* Gasket and Nut are packed separately in PE bags.



8Pin Male Connector
Female Pin PCB Layout
8 Pin 公接頭
PCB 挖孔位置尺寸圖





Recommended Panel Cut-out









PIN ASSIGNMENTS
FRONT VIEW 前視圖

UNIT: mm

TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE: Standard,Panel Lock 8Pin M Conn F Pin
SCALE: 1:1 | SIZE: A4 | SHEET: 1 OF 1
REV.: F | WC-REV.: A.3 | QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO: BDU-08PMFP-LC7001	DRAWN BY: Ruru	DATE: 2019-02-25
DWG NO: BDU-08PMFP-LC7001	CHECKED BY: Rita	DATE: 2019-02-25
CUSTOMER: ALTW	APPROVED BY: Max	DATE: 2019-02-25

W10814-03-RW01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.