



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C201735	2020/11/09	Ruru	△B X6
C	C210226	2021/03/30	Vicky	△C X4
D	C221995	2022/12/26	Vicky	△D X1



- △B△C
Note:
- * RoHS Compliant
 - * ∅ Important dimension
 - * △ Waterproof rate: IP68, mated 1m/24h
IP69K, mated
 - * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - O-Ring: Rubber, Green
 - Nut: Metal
 - Outer Mold: Thermoplastic, Black
 - * Cable: UL20549, PUR Jacket, Black
 - * Cable Length Tolerance:

0.5M < L ≤ 1M	: +60/-0 mm
1M < L ≤ 3M	: +120/-0 mm
3M < L ≤ 5M	: +160/-0 mm
5M < L ≤ 10M	: ±100 mm
10M < L ≤ 20M	: ±200 mm
20M < L ≤ 30M	: ±300 mm
30M < L ≤ 99M	: ±500 mm

UNIT:mm		TITLE	
TOLERANCE		ACC, SEN, A Code, DB-ENDED FF	
±0.5mm		SCALE 1:2	SIZE A4
		REV. D	WC-REV.
		SHEET 1 OF 2	
		∅∅:Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO		DRAWN BY		DATE	
		Ruru		2018-12-05	
DWG NO		CHECKED BY		DATE	
△B M12AXXFL-12AFL-SBXXX		Rita		2018-12-05	
CUSTOMER		APPROVED BY		DATE	
ALTW		Max		2018-12-05	

A