



1	2	3	4	5	6	7	8
F						REV.	DESCRIPTION
E							
D							
C							
B							
A							



Notes:  
\* DOL: Important Dimension.  
\* Waterproof Rate: IP68, IP69K.  
\* Connector: PU+GF, Black.  
\* Pin: Copper Alloy, Gold Plated.  
\* Screw Nut: Nylon, Black  
\* Outer Mold: PU, Black.  
\* Cable: (B) UL20549, PUR Jacket, Black.  
(D) UL2517, PVC Jacket, Black.  
\* Rated Voltage: 3 & 4Pin 250V dc. or ac.  
5Pin 60V dc. or ac.  
6~12Pin 30V dc. or ac.  
\* Rated Current: 3~5Pin 4A  
6~8Pin 2A  
10~12Pin 1.5A  
\* Cable Length Tolerance: 0.5±20mm  
01±40mm  
02M~05M:±60mm  
06M~10M:±100mm  
11M~30M:±200mm  
31M~99M:±500mm

UNIT:mm		TITLE M12 A-Code Double Ended			Amphenol LTW	ITEM NO	DRAWN BY Ruru	DATE 2018-12-05
TOLERANCE	± 0.5 mm	SCALE 1:2	SIZE A4	SHEET 1 OF 3	QC: Inspection item	DWG NO MSAPXXML-SAPFL-SXXXX	CHECKED BY Rita	DATE 2018-12-05
REV. A	WC-REV.					CUSTOMER ALTW	APPROVED BY Max	DATE 2018-12-05
1	2	3	4	5	6	7	8	W10814-03-AW01A2

	1	2	3	4	5	6	7	8
F								
E								
D								
C								
B								
A								



UNIT:mm			TITLE M12 A-Code Double Ended		
TOLERANCE	± 0.5 mm	SCALE	1:2	SIZE	A4
		REV.	A	WC-REV.	(QC): Inspection item

**Amphenol LTW**  
**安費諾亮泰企業股份有限公司**

ITEM NO	DRAWN BY	DATE
DWG NO	Ruru	2018-12-05
MSAPXXML-SAPFL-SXXXX	Rita	2018-12-05
CUSTOMER	APPROVED BY	DATE
ALTW	Max	2018-12-05

F

E

D

C

B

A

## Pin Assignments Front View

UNIT:mm			TITLE M12 A-Code Double Ended			<b>Amphenol LTW</b> <b>安費諾亮泰企業股份有限公司</b>	ITEM NO	DRAWN BY Ruru	DATE 2018-12-05
TOLERANCE  ± 0.5 mm			SCALE 1:2	SIZE A4	SHEET 3 OF 3		DWG NO MSAPXXML-SAPFL-SXXXX	CHECKED BY Rita	DATE 2018-12-05
			REV. A	WC-REV.	(QC): Inspection item		CUSTOMER ALTW	APPROVED BY Max	DATE 2018-12-05
				2	3		4	5	6