





Very Low Profile



Dimensions			
No of Positions	A	B	C
6	12.96	10.16	6.35
8	15.03	11.43	8.89
10	15.03	11.43	8.89

PCB LAYOUT/TOP VIEW



S
S
S
S

Materials

Housing: Standard Material Glass Filled Polyester UL 94V-0
Standard Color Black

Contact: 0.46mm (0.018") Diameter Alloy C5210. Gold Plating Over Nickel.

Ordering Information

Positions/Contacts	Description	W/O Flange	Shielded	SMT	SMT Shielded
6P6C	Very Low Profile	303066XFL	303066XFLS	303066XFLT	303066XFLTS
8P8C	Very Low Profile	303088XFL	303088XFLS	303088XFLT	303088XFLTS
10P10C	Very Low Profile	303080XFL	303080XFLS	303080XFLT	303080XFLTS

Standard contact plating is 15 micro inches of gold. For optional platings add dash number as follows: -6 = 6 Micro inches, -30 = 30 Micro inches, -50 = 50 Micro inches