

PRODUCT, FACILITY, & SAFETY IDENTIFICATION SOLUTIONS

COUNTRY/REGION

SEARCH

- WHAT'S NEW
- PRODUCTS BY CATEGORY
- PRODUCTS BY INDUSTRY
- SERVICES
- SUPPORT
- REGULATIONS/ COMPLIANCE
- LEAN MANUFACTURING & MAINTENANCE
- PRODUCT REGISTRATION

Home [Products By Category](#) [Printers & Supplies](#) [Benchtop Printers](#)
 Brady BBP™81 Label Printer **Brady BBP™81 Label Printer- 300 dpi Standard**

Brady BBP™81 Label Printer- 300 dpi Standard



The Brady **BBP™81** Label Printer provides enhanced productivity, along with the durability and reliability you need for tough industrial environments. Available in 300 dpi, the Brady **BBP81** printer produces sharp labels for a variety of applications. The **BBP81** printer is loaded with features including USB connectivity for plug-and-play simplicity, automatic calibration when the printer is turned on, and improved BradyConnect 10/100 Print Server with simultaneous use of parallel and Ethernet connections. The durable, die-cast metal frame provides a rugged platform for industrial printing in operations that require label production 12 hours/day, 5 days/week. The Brady **BBP81** printer is able to print a wide variety of materials, including paper, polyester, metalized polyester, polyimide, and PermaSleeve™ materials.

[Overview](#) [Specifications](#) [Accessories](#)

Print Resolution: 300 dpi
Print Speed: up to 8"/sec
Print Technology: Thermal Transfer
Application(s): Circuit Board Labeling, Data Communications Labeling, DoD UID, Facility, Safety & Maintenance Identification, General & Industrial Labeling, Healthcare Identification, Laboratory Identification, Panel Identification, Product Identification, Security Identification, Wire & Cable Marking

Max Labels Per Day: 5,000 labels/day
Hours of Operation: 12hrs / 5days
Max Label Width: 4.500"
Min Label Length: 0.500"
Max Print Width: 4.090"
Max Print Length: 32"
Max Liner Width: 4.500"
Min Liner Width: 1.000"
Color Capability: Single Color Printing
Bar Code Type: 2D and 1D (Linear)
PC Connectivity: Yes
Peripheral Printing: Yes
Stand Alone Printing: No
Connectivity Options: Parallel, Serial, USB 2.0, Ethernet 10/100

Portability: No
Memory: 16MB
Materials Supported: Gapped, Notched, Continuous, Tags,

RELATED INFORMATION

REQUEST A DEMO

- Labels
- Ribbons
- BBP81 Printer Driver**
- Bradysoft Printer Driver
- Quick Start Guide
- Product Literature
- User Manual
- BradyConnect 10/100 User Manual
- Technical Data
- Brady360 Comprehensive Customer Care
- Stress Free Printer Setup
- No Hassle Guarantee
- Knowledge Center
- Limited Warranty Terms & Conditions
- Product Registration
- Submit Product Feedback

Black Mark, Sleeves

Options: 10/100 Etherne

Weight: 32.400 lbs.

Warranty: 12 Months - See Terms and Conditions

 **Select New Product**

 **Email This Page**

 **Print This Page**

 **Contact Us**

 **Find a Distributor**

 **Join the Mailing List**

For more information on this product, contact Brady Customer Service or an Authorized Brady Distributor. Brady products are sold through distribution. Click on the "Find a Distributor" button to find a distributor near you.

*If you're not based in Canada, please contact your local Brady office for correct pricing.

Additional Information: [Privacy](#) | [Copyright](#) | [Site Map](#)

Copyright 2010 Brady Worldwide, Inc.