



Catalog Number: BPSPT-094-1-WT
Bulk TLS 2200®/TLS PC Link™ PermaSleeve™ Wire Marker Sleeves



Specifications:

Application(s): Panel Identification, Wire & Cable Marking

Agency Approval(s)/Compliance: MIL-STD-202, SAE-AS-81531, SAE-DTL-23053/5 Class 1, UL Recognized

Size: 1.015" W x 0.182" H (25.780 mm W x 4.620 mm H)

Range of Wire Diameter: 0.023" - 0.080" (0.58 mm - 2.03 mm)

Printable Sides: One-Sided Printable

Max Characters Per Line For Font #2: 22

Max Lines of Text For Font #2: 1

Shrink Ratio: 3-to-1

Label Type/Style: Sleeve

Color: White

Wire Gauge: 28 to 18

Finish: Matte

Qty Per Row: 1

Material Type: Polyolefin

Material Description: PermaSleeve™ Heat-Shrink Polyolefin

Suggested Ribbon Part#: R4310

Printer Compatibility: BMP71, TLS 2200, TLS-PC Link

Special Properties: Heat-shrinkable, Self-Extinguishing

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS

Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 2,500/Roll