



Part Number	Pieces Per Package	Material	Color	Labels Per Row	Label Width Inch (mm) A	Label Height Inch (mm) B	Horizontal Repeat Inch (mm) C	Vertical Repeat Inch (mm) D	Web Width Inch (mm) E
0.400" Label Width — 6 or 8 lines per inch									
DAT-179-619-10	10,000	Polyester	White	16	0.400 (10.16)	0.200 (5.08)	0.500 (12.70)	0.250 (6.35)	8.900 (226.06)
DAT-179-652-10	10,000	Polyimide	Amber	16	0.400 (10.16)	0.200 (5.08)	0.500 (12.70)	0.250 (6.35)	8.900 (226.06)
0.500" Label Width — 6 or 8 lines per inch									
DAT-67-499-10	10,000	Nylon Cloth	White	12	0.500 (12.70)	0.750 (19.05)	0.600 (15.24)	1.000 (25.40)	8.100 (205.74)
DAT-67-502-10	10,000	Vinyl Cloth	White	12	0.500 (12.70)	0.750 (19.05)	0.600 (15.24)	1.000 (25.40)	8.100 (205.74)
DAT-68-632-10	10,000	Polyvinylfluoride	White	12	0.500 (12.70)	0.750 (19.05)	0.600 (15.24)	1.000 (25.40)	8.100 (205.74)
DAT-31-502*-10	10,000	Vinyl Cloth	White	14	0.500 (12.70)	0.750 (19.05)	0.600 (15.24)	1.000 (25.40)	9.300 (236.22)
DAT-32-632*-10	10,000	Polyvinylfluoride	White	14	0.500 (12.70)	0.750 (19.05)	0.600 (15.24)	1.000 (25.40)	9.300 (236.22)
DAT-21-110-10	10,000	Saturated Paper	White	12	0.500 (12.70)	1.437 (36.50)	0.600 (15.24)	1.500 (38.10)	8.100 (205.74)
DAT-24-502-10	10,000	Vinyl Cloth	White	12	0.500 (12.70)	1.437 (36.50)	0.600 (15.24)	1.500 (38.10)	8.100 (205.74)
0.500" Label Width — 6 or 8 lines per inch — Square Corners									
DAT-43-502-10	10,000	Vinyl Cloth	White	16	0.500 (12.70)	0.437 (11.10)	0.500 (12.70)	0.500 (12.70)	9.000 (228.60)
DAT-44-607-10	10,000	Tamper-Resistant Vinyl	White	16	0.500 (12.70)	0.437 (11.10)	0.500 (12.70)	0.500 (12.70)	9.000 (228.60)
DAT-45-619-10	10,000	Polyester	White	16	0.500 (12.70)	0.437 (11.10)	0.500 (12.70)	0.500 (12.70)	9.000 (228.60)
DAT-46-693-10	10,000	Metallized Polyester	Silver	16	0.500 (12.70)	0.437 (11.10)	0.500 (12.70)	0.500 (12.70)	9.000 (228.60)
DAT-46-969-10	10,000	Metallized Polyester	Silver	16	0.500 (12.70)	0.437 (11.10)	0.500 (12.70)	0.500 (12.70)	9.000 (228.60)
DAT-98-673-10	10,000	Polyester	Silver	16	0.500 (12.70)	0.437 (11.10)	0.500 (12.70)	0.500 (12.70)	9.000 (228.60)
DAT-143-502-10	10,000	Vinyl Cloth	White	16	0.500 (12.70)	0.937 (23.80)	0.500 (12.70)	1.000 (25.40)	9.000 (228.60)
DAT-144-632-10	10,000	Polyvinylfluoride	White	16	0.500 (12.70)	0.937 (23.80)	0.500 (12.70)	1.000 (25.40)	9.000 (228.60)
DAT-171-652-10	10,000	Polyimide	Amber	16	0.500 (12.70)	0.437 (11.10)	0.500 (12.70)	0.500 (12.70)	9.000 (228.60)
0.650" Label Width — 6 or 8 lines per inch									
DAT-15-502-1-10	10,000	Vinyl Cloth	White	10	0.650 (16.51)	0.200 (5.08)	0.800 (20.32)	0.250 (6.35)	8.850 (224.79)
DAT-16-607-10	10,000	Tamper-Resistant Vinyl	White	10	0.650 (16.51)	0.200 (5.08)	0.800 (20.32)	0.250 (6.35)	8.850 (224.79)
DAT-17-619-10	10,000	Polyester	White	10	0.650 (16.51)	0.200 (5.08)	0.800 (20.32)	0.250 (6.35)	8.850 (224.79)
DAT-56-637-10	10,000	Tedlar®	White	10	0.650 (16.51)	0.200 (5.08)	0.800 (20.32)	0.250 (6.35)	8.850 (224.79)
DAT-58-652-10	10,000	Polyimide	Amber	10	0.650 (16.51)	0.200 (5.08)	0.800 (20.32)	0.250 (6.35)	8.850 (224.79)
DAT-88-693-10	10,000	Polyester	Silver	10	0.650 (16.51)	0.200 (5.08)	0.800 (20.32)	0.250 (6.35)	8.850 (224.79)
DAT-88-969-10	10,000	Polyester	Silver	10	0.650 (16.51)	0.200 (5.08)	0.800 (20.32)	0.250 (6.35)	8.850 (224.79)
DAT-109-658-10	10,000	Polyimide	Amber	10	0.650 (16.51)	0.200 (5.08)	0.800 (20.32)	0.250 (6.35)	8.850 (224.79)
DAT-111-164-10	10,000	Polyester	Silver	10	0.650 (16.51)	0.200 (5.08)	0.800 (20.32)	0.250 (6.35)	8.850 (224.79)
0.750" Label Width — 6 lines per inch									
DAT-25-502-10	10,000	Vinyl Cloth	White	9	0.750 (19.05)	0.250 (6.35)	0.900 (22.86)	0.330 (8.46)	9.000 (228.60)
DAT-26-607-10	10,000	Tamper-Resistant Vinyl	White	9	0.750 (19.05)	0.250 (6.35)	0.900 (22.86)	0.330 (8.46)	9.000 (228.60)
DAT-27-619-10	10,000	Polyester	White	9	0.750 (19.05)	0.250 (6.35)	0.900 (22.86)	0.330 (8.46)	9.000 (228.60)
DAT-89-969-10	10,000	Polyester	Silver	9	0.750 (19.05)	0.250 (6.35)	0.900 (22.86)	0.330 (8.46)	9.000 (228.60)
DAT-96-652-10	10,000	Polyimide	Amber	9	0.750 (19.05)	0.250 (6.35)	0.900 (22.86)	0.330 (8.46)	9.000 (228.60)
DAT-110-658-10	10,000	Polyimide	Amber	9	0.750 (19.05)	0.250 (6.35)	0.900 (22.86)	0.330 (8.46)	9.000 (228.60)
DAT-112-164-10	10,000	Polyester	Silver	9	0.750 (19.05)	0.250 (6.35)	0.900 (22.86)	0.330 (8.46)	9.000 (228.60)
DAT-161-637-10	10,000	Polyvinylfluoride	White	9	0.750 (19.05)	0.250 (6.35)	0.900 (22.86)	0.330 (8.46)	9.000 (228.60)

Tedlar® is a registered trademark of DuPont.

* Size does not fit narrow carriage (80-column) printers. See p. 158 for identical narrow carriage labels.

Note: Labels in chart are sorted in order by height, 3 digit material number (within part number), then die number (within part number).