




Catalog Number: DAT-45-619-10

DATAB® Dot Matrix Printable Labels



Application(s): Circuit Board & Component ID, Through Hole - Top

Size: 0.500" W x 0.437" H (12.700 mm W x 11.100 mm H)

Printable Area: 0.500" W x 0.437" H (12.700 mm W x 11.100 mm H)

Web Width: 9.000" (228.60 mm)

Label Type/Style: Label

Vertical Repeat: 0.500" (12.70 mm)

Horizontal Repeat: 0.500" (12.70 mm)

Color: White

Finish: Matte

Qty Per Row: 16

Material Type: Polyester

Material Description: Permanent Polyester

Recommended Ribbon Series: R5000, R2000

After Process: Yes, this material will work with this application

Lines Per Inch: 6 or 8 lines per inch

Printer Compatibility: Dot Matrix Printers, Sleeve & Datab Series

Style: Fan-folded, Square Corners, Butt-Cut

Surface Mount Technology: No, this material does not work with this application

Through Hole Technology: Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 10,000/Package