



Product Number: JET-23-115-5

Blank, printable vinyl cloth labels for Ink Jet printers.



Application(s):	Circuit Board & Component ID, Through Hole - Top
Size:	0.375" W x 2.000" H (9.530 mm W x 50.800 mm H)
Printable Area:	0.375" W x 2.000" H (9.530 mm W x 50.800 mm H)
Label Type/Style:	Label
Horizontal Repeat:	0.470" (11.93 mm)
Color:	White
Finish:	Matte
Qty Per Row:	17
Material Type:	Vinyl Cloth
Material Description:	Repositionable Vinyl Cloth
After Process:	Yes, this material will work with this application
Left Margin:	0.300" (7.62 mm)
Printer Compatibility:	Ink Jet Printers
Qty Per Sheet:	68
Surface Mount Technology:	No, this material does not work with this application
Through Hole Technology:	Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No
Top Margin:	0.750" (19.05 mm)
Special Properties:	Repositionable
RoHS Compatibility:	Compliant with RoHS Directive. NOTE: All statements

concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 5,000/Package
