



Catalog Number: LAT-29-747-10-YL

LASERTAB® Laser Printable Labels



Specifications:

Application(s): Circuit Board & Component ID, Through Hole - Top

Size: 0.650" W x 0.200" H (16.510 mm W x 5.080 mm H)

Sheet Size: 8.500" x 11.000" (215.9 mm x 279.4 mm)

Printable Area: 0.650" W x 0.200" H (16.510 mm W x 5.080 mm H)

Label Type/Style: Label

Horizontal Repeat: 0.800" (20.32 mm)

Color: Yellow

Finish: Matte

Qty Per Row: 10

Material Type: Polyester

Material Description: Permanent Polyester

After Process: Yes, this material will work with this application

Left Margin: 0.325" (8.26 mm)

Printer: Laser Printers

Compatibility:

Qty Per Sheet: 480

Surface Mount Technology: No, this material does not work with this application

Through Hole Technology: Top: Yes, Bottom: Yes

Top Margin: 0.875" (22.23 mm)

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw

materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 10,000/Package