



Catalog Number: M71-88-427

BMP71 Labels



This material is UL recognized with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

Application(s): Communications Cables, Panel Identification, Voice/Data Identification, Wire & Cable Marking

Agency: UL Recognized

Approval(s)/Compliance:

Size: 1.750" W x 1.500" H (44.450 mm W x 38.100 mm H)

Printable Area: 1.750" W x 0.500" H (44.450 mm W x 12.700 mm H)

Max Characters Per Line 40
For Font #2:

Max Lines of Text For 5
Font #2:

Label Type/Style: Self-Laminating Label

Color: White/Translucent

Wire Gauge: 10 to 4

Finish: Matte

Qty Per Row: 1

Material Type: Vinyl

Material Description: Self-Laminating Vinyl

Recommended Ribbon M71-R4300 BK
Series:

Acceptable Ribbon Series: M71-R6200

Cable Type: 4 Pair UTP, CAT 5

Printer Compatibility: BMP71

Special Properties: Excellent abrasion and smudge resistance, Excellent water & oil resistance, Self-Extinguishing, Self-Laminating

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 250/Roll