



Product Number: PTL-8-428

TLS 2200®/TLS PC Link™ Labels



Specifications:

Application(s):	General & Industrial Identification, General Identification, Panel Identification, Through Hole – Top
Agency Approval (s)/Compliance:	AGA Approved, CSA Approved, Halogen-Free (DIN VDE 0472/parts 815), UL Recognized
Size:	0.500" W x 50' H (12.700 mm W x 15.240 m H)
Printable Area:	0.500" W x 50' H (12.700 mm W x 15.240 m H)
Max Characters Per Line For Font #2:	5
Max Lines of Text For Font #2:	5
Label Type/Style:	Label
Color:	Silver
Finish:	Matte
Qty Per	Row: 1
Material Type:	Polyester
Material Description:	Metallized Polyester

Brady Material #: [B-428](#)

Recommended Ribbon Series: R4310

Suggested Ribbon Part#: R4310

After Process: Yes, this material will work with this application

Printer Compatibility: BMP71, TLS 2200, TLS-PC Link