



**Catalog Number: PTL-83-499**

**TLS 2200®/TLS PC Link™ Labels**



**Description:**

Labels for the TLS 2200® & TLS-PC Link™ Thermal Transfer Portable Printers. Please Note: This material is UL approved with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

**Specification:**

**Application(s):** Laboratory Identification, Vial, Vial Top

**Agency Approval(s)/Compliance:** Halogen-Free (DIN VDE 0472/parts 815), UL Recognized

**Printable Area:** 0.500" Diameter (12.700 mm Diameter)

**Max Characters Per Line For Font #2:** 11

**Max Lines of Text For Font #2:** 1

**Label Type/Style:** Label

**Color:** White

**Finish:** Matte

**Qty Per Row:** 1

**Material Type:** Nylon Cloth

**Material Description:** Nylon Cloth

**Recommended Ribbon Series:** R4310

**Acceptable Ribbon Series:** R6210

**Environment:** Autoclave, Freezer, Liquid Nitrogen

**Printer Compatibility:** BMP71, TLS 2200, TLS-PC Link

**Surface:** Highly Textured, Low Surface Energy, Powder Coated, Smooth, Textured/Rough

**Special Properties:** High adhesion, Low profile

**RoHS Compatibility:** Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

**QTY/UOM:** 500/Roll