



Part Number	Pieces Per Package	Material	Color	Labels Per Row	Label Width Inch (mm) A	Label Height Inch (mm) B	Horizontal Repeat Inch (mm) C	Vertical Repeat Inch (mm) D	Web Width Inch (mm) E	Recommended Ribbon
0.750" Label Width (Cont.)										
THT-1-477-10	10,000	Polyimide	White	4	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	0.350 (8.89)	3.350 (85.09)	R6002
THT-46-477-10	10,000	Polyimide	White	1	0.750 (19.05)	0.250 (6.35)	—	0.350 (8.89)	0.950 (24.13)	R6006
THT-1-478-10	10,000	Polyimide	White	4	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	0.350 (8.89)	3.350 (85.09)	R6002
THT-1-498-10	10,000	Vinyl Cloth	White	4	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	0.350 (8.89)	3.350 (85.09)	R4311
THT-46-478-10	10,000	Polyimide	White	1	0.750 (19.05)	0.250 (6.35)	—	0.350 (8.89)	0.950 (24.13)	R6006
THT-1-479-10	10,000	Polyimide	White	4	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	0.350 (8.89)	3.350 (85.09)	R6002
THT-46-479-10	10,000	Polyimide	White	1	0.750 (19.05)	0.250 (6.35)	—	0.350 (8.89)	0.950 (24.13)	R6006
THT-1-487-10	10,000	Polyimide	White	4	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	0.350 (8.89)	3.350 (85.09)	R6002
THT-46-487-10	10,000	Polyimide	White	1	0.750 (19.05)	0.250 (6.35)	—	0.350 (8.89)	0.950 (24.13)	R6006
THT-1-488-10	10,000	Polyester	White	4	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	0.350 (8.89)	3.350 (85.09)	R4300
THT-1-495-10	10,000	PEN	White	4	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	0.350 (8.89)	3.350 (85.09)	R6002
THT-46-495-10	10,000	PEN	White	1	0.750 (19.05)	0.250 (6.35)	—	0.350 (8.89)	0.950 (24.13)	R6006
THT-1-497-10	10,000	Polyimide	White	4	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	0.350 (8.89)	3.350 (85.09)	R6002
THT-46-497-10	10,000	Polyimide	White	1	0.750 (19.05)	0.250 (6.35)	—	0.350 (8.89)	0.950 (24.13)	R6006
XHT-1-8423-10	10,000	Polyester	White	4	0.750 (19.05)	0.250 (6.35)	0.800 (20.32)	0.350 (8.89)	3.350 (85.09)	R6202
THT-50-423-10	10,000	Polyester	White	4	0.750 (19.05)	0.750 (19.05)	0.800 (20.32)	0.875 (22.23)	3.350 (85.09)	R6002
THT-50-426-10	10,000	Polyimide	Amber	4	0.750 (19.05)	0.750 (19.05)	0.800 (20.32)	0.875 (22.23)	3.350 (85.09)	R4300
THT-91-498-5	5,000	Vinyl Cloth	White	4	0.750 (19.05)	0.937 (23.8)	0.875 (22.23)	1.062 (26.98)	3.500 (88.90)	R4300
0.800" Label Width										
THT-95-498-5	5,000	Vinyl Cloth	White	3	0.800 (20.32)	1.437 (36.50)	0.900 (22.86)	1.562 (39.68)	2.800 (71.12)	R4300
THT-69-499-3	3,000	Nylon Cloth	White	2	0.800 (20.32)	1.437 (36.50)	0.900 (22.86)	1.540 (39.12)	1.900 (48.26)	R4902
THT-162-499-10	10,000	Nylon Cloth	White	4	0.800 (20.32)	1.437 (36.50)	0.600 (15.24)	1.562 (39.67)	3.700 (93.98)	R4902
0.900" Label Width										
THT-2-423-10	10,000	Polyester	White	3	0.900 (22.86)	0.250 (6.35)	1.125 (28.58)	0.350 (8.89)	3.350 (85.09)	R6002
THT-49-423-10	10,000	Polyester	White	1	0.900 (22.86)	0.250 (6.35)	—	0.350 (8.89)	1.100 (27.94)	R6006
THT-2-426-10	10,000	Polyimide	Amber	3	0.900 (22.86)	0.250 (6.35)	1.125 (28.58)	0.350 (8.89)	3.350 (85.09)	R4300
THT-49-426-10	10,000	Polyimide	Amber	1	0.900 (22.86)	0.250 (6.35)	—	0.350 (8.89)	1.100 (27.94)	R4311
THT-2-437-10	10,000	Tedlar®	White	3	0.900 (22.86)	0.250 (6.35)	1.125 (28.58)	0.350 (8.89)	3.350 (85.09)	R4300
THT-2-457-10	10,000	Polyimide	White	3	0.900 (22.86)	0.250 (6.35)	1.125 (28.58)	0.350 (8.89)	3.350 (85.09)	R6002
THT-49-457-10	10,000	Polyimide	White	1	0.900 (22.86)	0.250 (6.35)	—	0.350 (8.89)	1.100 (27.94)	R6006
THT-2-473-10	10,000	Polyester	White	3	0.900 (22.86)	0.250 (6.35)	1.125 (28.58)	0.350 (8.89)	3.350 (85.09)	R6002
THT-49-473-10	10,000	Polyester	White	1	0.900 (22.86)	0.250 (6.35)	—	0.350 (8.89)	1.100 (27.94)	R6006
THT-2-478-10	10,000	Polyester	White	3	0.900 (22.86)	0.250 (6.35)	1.125 (28.58)	0.350 (8.89)	3.350 (85.09)	R6002
THT-49-478-10	10,000	Polyester	White	1	0.900 (22.86)	0.250 (6.35)	—	0.350 (8.89)	1.100 (27.94)	R6006
THT-2-479-10	10,000	Polyester	White	3	0.900 (22.86)	0.250 (6.35)	1.125 (28.58)	0.350 (8.89)	3.350 (85.09)	R6002
THT-49-479-10	10,000	Polyester	White	1	0.900 (22.86)	0.250 (6.35)	—	0.350 (8.89)	1.100 (27.94)	R6006
THT-2-488-10	10,000	Polyester	White	3	0.900 (22.86)	0.250 (6.35)	1.125 (28.58)	0.350 (8.89)	3.350 (85.09)	R4300
THT-2-495-10	10,000	PEN	White	3	0.900 (22.86)	0.250 (6.35)	1.125 (28.58)	0.350 (8.89)	3.350 (85.09)	R4300
THT-49-495-10	10,000	PEN	White	3	0.900 (22.86)	0.250 (6.35)	1.125 (28.58)	0.350 (8.89)	3.350 (85.09)	R4300
XHT-2-8423-10	10,000	Polyester	White	3	0.900 (22.86)	0.250 (6.35)	1.125 (28.58)	0.350 (8.89)	3.350 (85.09)	R6202
THT-125-499-3	3,000	Nylon Cloth	White	1	0.900 (22.86)	0.500 (12.70)	—	1.000 (25.40)	1.100 (27.94)	R4306
THT-126-499-3x	3,000	Nylon Cloth	White	2	0.900 (22.86)	0.500 (12.70) dia.	0.500 (12.70)	0.600 (15.24)	1.700 (43.18)	R4302
THT-140-488-3	3,000	Polyester	White	2	0.900 (22.86)	0.750 (19.05)	—	0.875 (22.23)	2.100 (53.34)	R4306
THT-141-488-3	3,000	Polyester	White	2	0.900 (22.86)	0.900 (22.86)	—	1.000 (25.40)	2.100 (53.34)	R4306
THT-164-488-1	1,000	Polyester	White	1	0.900 (22.86)	0.900 (22.86)	—	1.000 (25.40)	1.100 (27.94)	R4306
1.000" Label Width										
THT-42-354-10	10,000	Polyester/Paper	White	1	1.000 (25.40)	0.187 (4.75)	—	0.287 (7.29)	1.200 (30.48)	R6206
THT-41-423-10	10,000	Polyester	White	3	1.000 (25.40)	0.187 (4.75)	1.075 (27.31)	0.287 (7.29)	3.350 (85.09)	R6002
THT-42-423-10	10,000	Polyester	White	1	1.000 (25.40)	0.187 (4.75)	—	0.287 (7.29)	1.200 (30.48)	R6006
THT-41-426-10	10,000	Polyimide	Amber	3	1.000 (25.40)	0.187 (4.75)	1.075 (27.31)	0.287 (7.29)	3.350 (85.09)	R4300
THT-42-426-10	10,000	Polyimide	Amber	1	1.000 (25.40)	0.187 (4.75)	—	0.287 (7.29)	1.200 (30.48)	R4306
THT-42-457-10	10,000	Polyimide	White	1	1.000 (25.40)	0.187 (4.75)	—	0.287 (7.29)	1.200 (30.48)	R6006

Note: Labels in chart are sorted in order by width, height, 3 or 4 digit material number (within part number), then die number (within part number).

Tedlar® is a registered trademark of DuPont.