



**Catalog Number:** THT-107-483

**Thermal Transfer Printable Labels**

**Specifications**

**Application(s):** General & Industrial Identification, General ID, General Identification, Panel Identification, Voice/Data Identification

**Agency Approval(s)/Compliance:** CSA Approved, UL Recognized

**Size:** 4.000" W x 300' H (101.600 mm W x 91.440 m H)

**Printable Area:** 4.000" W x 300' H (101.600 mm W x 91.440 mm H)

**Web Width:** 4.200" (106.68 mm)

**Label Type/Style:** Label

**Vertical Repeat:** 300' (91.44 m)

**Color:** White

**Finish:** Gloss

**Qty Per Row:** 1

**Material Type:** Polyester

**Material Description:** Ultra Aggressive Polyester

**Recommended Ribbon Series:** 6000

**Suggested Ribbon Part#:** R6007

**Acceptable Ribbon Series:** 6200, 4900, 4400 (colors)

**Printer Compatibility:** BBP81, Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 300X-Plus II, Brady 3481, Brady 360X-Plus II, Brady 600X-Plus II, Brady 6441, Brady IP, Tagus T200, Tagus T300, Thermal Transfer Printers

**Surface:** Highly Textured, Low Surface Energy, Powder Coated, Smooth, Textured/Rough

**Special Properties:** Designed for powder coated surfaces, Ultra-aggressive adhesive

**RoHS Compatibility:** Compliant with RoHS Directive. NOTE: All statements

concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

**QTY/UOM:** 1/Roll