



Catalog Number: THT-18-428-3

Thermal Transfer Printable Labels



Printable, metallized polyester labels for thermal transfer printers. Please Note: This material is UL, CSA & AGA approved with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

Specifications:

Application(s): General & Industrial Identification, Through Hole - Top

Agency AGA Approved, CSA Approved, Halogen-Free (DIN VDE 0472/parts

Approval(s)/Compliance: 815), UL Recognized

Size: 3.000" W x 1.000" H (76.200 mm W x 25.400 mm H)

Printable Area: 3.000" W x 1.000" H (76.200 mm W x 25.400 mm H)

Web Width: 3.200" (81.28 mm)

Label Type/Style: Label

Vertical Repeat: 1.125" (28.58 mm)

Color: Silver

Finish: Matte

Qty Per Row: 1

Material Type: Polyester

Material Description: Metallized Polyester

Recommended Ribbon Series: 4300

Suggested Ribbon Part#: R4300

Acceptable Ribbon Series: 6200, 4500 (colors)

After Process: Yes, this material will work with this application

Printer Compatibility: BBP81, Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 300X-Plus II, Brady 3481, Brady 360X-Plus II, Brady 600X-Plus II, Brady 6441, Brady IP, Tagus T200, Tagus T300, Thermal Transfer Printers

Surface: Smooth

Surface Mount Technology: No, this material does not work with this application

Through Hole Technology: Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 3,000/Roll