



**Product Number: THT-73-427-10**

**Thermal Transfer Printable Labels**



**Specifications:**

Application(s):	Panel Identification, Wire & Cable Marking
Agency Approval(s)/ Compliance:	UL Recognized
Size:	0.750" W x 1.750" H (19.050 mm W x 44.450 mm H)
Printable Area:	0.750" W x 0.500" H (19.050 mm W x 12.700 mm H)
Web Width:	3.350" (85.09 mm)
Label Type/Style:	Self-Laminating Label
Vertical Repeat:	1.875" (47.63 mm)
Horizontal Repeat:	0.800" (20.32 mm)
Color:	White/Translucent
Finish:	Matte
Qty Per Row:	4
Material Type:	Vinyl
Material Description:	Self-Laminating Vinyl
Brady Material #:	<a href="#">B-427</a>
Recommended Ribbon Series:	4300
Suggested Ribbon Part#:	R4300

Acceptable Ribbon Series:	6200, 4500 (colors)
Printer Compatibility:	BBP81, Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 300XPlus II, Brady 3481, Brady 360X-Plus II, Brady 600X-Plus II, Brady 6441, Brady IP, Tagus T200, Tagus T300, Thermal Transfer Printers
Style:	Roll-Form, Radius Corners
Special Properties:	Excellent abrasion and smudge resistance, Excellent water & oil resistance, Self-Extinguishing, Self-Laminating
RoHS Compatibility:	Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.
QTY/UOM:	10,000/Roll