

Labels Index by Part Number

*Call for larger quantity pricing.

Mfr.'s Type	Qty/ Roll	Labels/ Row	Size W x H (in.)	Material Number	Each Roll (1-9)*	Mfr.'s Type	Qty/ Roll	Labels/ Row	Size W x H (in.)	Material Number	Each Roll (1-9)*
THT-72-478-10	10,000	1	1.750 x 0.250	B-478	702.20	THT-103-478-10	10,000	1	1.000 x 0.250	B-478	346.30
THT-72-479-10	10,000	1	1.750 x 0.250	B-479	702.20	THT-103-479-10	10,000	1	1.000 x 0.250	B-479	346.30
THT-72-495-10	10,000	1	1.750 x 0.250	B-495	561.60	THT-103-487-10	10,000	1	1.000 x 0.250	B-487	433.00
THT-72-497-10	10,000	1	1.750 x 0.250	B-497	702.20	THT-103-495-10	10,000	1	1.000 x 0.250	B-495	277.00
THT-73-427-10	10,000	4	0.750 x 1.750	B-427	462.50	THT-103-497-10	10,000	1	1.000 x 0.250	B-497	346.30
THT-74-427-10	10,000	4	0.800 x 1.437	B-427	336.60	THT-104-497-20	20,000	6	0.315 x 0.177	B-497	482.70
THT-75-427-3	3,000	2	1.000 x 2.250	B-427	193.80	THT-105-437	1	1	1.500 x 300 ft	B-437	259.30
THT-76-422-1	1,000	1	4.000 x 3.000	B-422	214.50	THT-105-437-YL	1	1	1.500 x 300 ft	B-437	259.30
THT-76-449-1	1,000	1	4.000 x 3.000	B-449	121.50	THT-106-423	1	1	2.000 x 300 ft	B-423	108.20
THT-76-483-1	1,000	1	4.000 x 3.000	B-483	209.00	THT-106-428	1	1	2.000 x 300 ft	B-428	165.60
THT-76-489-1	1,000	1	4.000 x 3.000	B-489	213.50	THT-106-439	1	1	2.000 x 300 ft	B-439	108.20
THT-77-402-1.4	1,400	1	4.000 x 4.000	B-402	34.00	THT-106-483	1	1	2.000 x 300 ft	B-483	129.90
THT-78-402-0.9	900	1	4.000 x 6.500	B-402	34.50	THT-106-486	1	1	2.000 x 300 ft	B-486	198.60
THT-78-408-1	1,000	1	4.000 x 6.500	B-408	193.40	THT-107-423	1	1	4.000 x 300 ft	B-423	201.80
THT-79-423-10	10,000	1	2.000 x 0.400	B-423	152.90	THT-107-428	1	1	4.000 x 300 ft	B-428	308.70
THT-80-427-5	5,000	4	0.500 x 0.750	B-427	79.90	THT-107-439	1	1	4.000 x 300 ft	B-439	201.80
THT-81-427-1	1,000	2	1.000 x 6.000	B-427	186.10	THT-107-483	1	1	4.000 x 300 ft	B-483	242.10
THT-82-427-0.5	500	1	2.000 x 6.000	B-427	164.20	THT-107-486	1	1	4.000 x 300 ft	B-486	370.40
THT-83-427-0.5	500	1	2.000 x 7.000	B-427	196.70	THT-113-427-5	5,000	4	0.500 x 1.000	B-427	87.50
THT-84-427-3	3,000	1	1.000 x 6.000	B-427	468.00	THT-114-427-5	5,000	4	0.500 x 1.250	B-427	93.80
THT-85-427-2	2,000	1	2.000 x 6.000	B-427	550.90	THT-115-427-5	5,000	2	1.000 x 0.750	B-427	112.50
THT-86-427-2	2,000	1	2.000 x 7.000	B-427	659.50	THT-116-427-5	5,000	2	1.000 x 1.000	B-427	150.00
THT-87-498-5	5,000	6	0.500 x 1.437	B-498	210.60	THT-118-427-5	5,000	1	1.500 x 1.000	B-427	206.30
THT-88-498-5	5,000	2	1.000 x 0.750	B-498	234.70	THT-119-427-2.5	2,500	1	1.500 x 1.500	B-427	154.70
THT-89-498-5	5,000	3	1.000 x 1.437	B-498	361.70	THT-120-427-5	5,000	1	1.750 x 1.000	B-427	240.60
THT-90-498-5	5,000	6	0.250 x 1.437	B-498	177.90	THT-121-427-2.5	2,500	1	1.750 x 1.500	B-427	180.50
THT-91-498-5	5,000	4	0.750 x 0.937	B-498	201.60	THT-122-461-3	3,000	1	1.800 x 0.500	B-461	88.20
THT-92-498-2	1	1	0.375 x 165 ft	B-498	134.20	THT-123-461-3	3,000	1	1.800 x 0.375	B-461	67.30
THT-93-498-2	1	1	0.318 x 165 ft	B-498	134.20	THT-125-499-3	3,000	1	0.900 x 0.500	B-499	82.60
THT-94-498-2	1	1	0.240 x 165 ft	B-498	134.20	THT-126-499-3	3,000	2	0.900 x 0.500	B-499	109.50
THT-95-498-5	5,000	3	0.800 x 1.437	B-498	254.80	THT-127-427-3	3,000	1	2.200 x 0.500	B-427	107.10
THT-96-473-10	10,000	4	0.500 x 0.275	B-476	72.50	THT-127-461-3	3,000	1	2.200 x 0.500	B-461	107.10
THT-96-477-10	10,000	4	0.500 x 0.275	B-477	268.10	THT-131-461-3	3,000	1	2.625 x 1.000	B-461	214.20
THT-96-487-10	10,000	4	0.500 x 0.275	B-487	268.10	THT-135-427-3-AW	3,000	1	1.500 x 0.750	B-427	106.70
THT-96-497-10	10,000	4	0.500 x 0.275	B-497	214.40	THT-136-499-3	3,000	1	1.500 x 0.750	B-499	140.00
THT-97-423-10	10,000	1	0.500 x 0.200	B-423	41.60	THT-137-427-3-AW	3,000	1	2.000 x 1.000	B-427	173.40
THT-97-457-10	10,000	1	0.500 x 0.200	B-457	239.00	THT-137-499-3	3,000	1	2.000 x 1.000	B-499	235.60
THT-97-473-10	10,000	1	0.500 x 0.200	B-473	61.50	THT-140-488-3	3,000	1	0.900 x 0.750	B-488	48.50
THT-97-477-10	10,000	1	0.500 x 0.200	B-477	239.00	THT-141-488-3	3,000	1	0.900 x 0.900	B-488	58.10
THT-97-478-10	10,000	1	0.500 x 0.200	B-478	191.20	THT-142-423-2.5	2,500	1	2.250 x 0.200	B-423	42.50
THT-97-479-10	10,000	1	0.500 x 0.200	B-479	191.20	THT-143-499-3	3,000	4	0.375 dia.	B-499	63.30
THT-97-487-10	10,000	1	0.500 x 0.200	B-487	239.00	THT-144-499-3	3,000	3	0.500 dia.	B-499	63.30
THT-97-495-10	10,000	1	0.500 x 0.200	B-495	152.90	THT-151-499-3	3,000	1	2.000 x 0.250	B-499	94.60
THT-97-497-10	10,000	1	0.500 x 0.200	B-497	191.20	THT-152-499-3	3,000	1	1.000 x 0.375	B-499	73.40
THT-99-473-10	10,000	1	0.500 x 0.500	B-473	97.70	XHTHT-1-8423-10	10,000	4	0.750 x 0.250	B-8423	30.10
THT-99-477-10	10,000	1	0.500 x 0.500	B-477	581.70	XHTHT-2-8423-10	10,000	3	0.900 x 0.250	B-8423	40.60
THT-99-478-10	10,000	1	0.500 x 0.500	B-478	465.30	XHTHT-3-8423-10	10,000	3	1.000 x 0.375	B-8423	45.50
THT-99-479-10	10,000	1	0.500 x 0.500	B-479	465.30	XHTHT-4-8423-10	10,000	2	1.500 x 0.250	B-8425	47.90
THT-99-487-10	10,000	1	0.500 x 0.500	B-487	581.70	XHTHT-5-8423-10	10,000	3	1.000 x 0.500	B-8423	64.90
THT-99-495-10	10,000	1	0.500 x 0.500	B-495	372.20	XHTHT-5-8425-10	10,000	3	1.000 x 0.500	B-8425	48.70
THT-99-497-10	10,000	1	0.500 x 0.500	B-497	465.30	XHTHT-17-8423-5	5,000	1	2.000 x 1.000	B-8423	101.30
THT-100-473-10	10,000	1	0.700 x 0.375	B-473	70.80	XHTHT-17-8425-5	5,000	1	2.000 x 1.000	B-8425	76.00
THT-102-422-10	10,000	1	1.500 x 3.700	B-422	125.60	XHTHT-18-8423-5	5,000	1	3.000 x 1.000	B-8423	150.70
THT-103-423-10	10,000	1	1.000 x 0.250	B-423	63.90	XHTHT-18-8425-5	5,000	1	3.000 x 1.000	B-8425	113.00
THT-103-426-10	10,000	1	1.000 x 0.250	B-426	433.00	XHTHT-19-8423-3	3,000	1	3.000 x 2.000	B-8423	168.80
THT-103-457-10	10,000	1	1.000 x 0.250	B-457	433.00	XHTHT-19-8425-3	3,000	1	3.000 x 2.000	B-8425	126.60
THT-103-473-10	10,000	1	1.000 x 0.250	B-473	92.40	XHTHT-55-8423-3	3,000	1	4.000 x 2.000	B-8423	232.20
THT-103-477-10	10,000	1	1.000 x 0.250	B-477	433.00	XHTHT-55-8425-3	3,000	1	4.000 x 2.000	B-8425	174.20

Thermal Transfer Labels

Brady

Thermal Transfer Printer Materials Chart

Type	Max Service Temp. °F	Color/Finish	Use and Special Properties	Approvals
Glass Cloth				
B-520	932 (10 min.)	White/Matte	For high temperature work in process ID. Label is pressure sensitive at room temp. & becomes permanently fixed at temperatures above 752°F.	-
Nylon Cloth				
B-499	194 (30 days)	White/Matte	For wire & electronic component marking. Permanent adhesive.	UL
Paper				
B-402	158 (30 days)	White/Matte	For bar code & general labeling. Aggressive adhesive for bonding corrugated, films, plastic & steel.	-
B-408	70 (30 days)	White/Matte	For bar code & general labeling. Repositionable adhesive.	-
B-424	158 (30 days)	White/Matte	For bar code & general labeling. Good contrast & smear resistance.	-
Polyester				
B-422	248 (10 min.)	White/Gloss	For electronic PCB & component; bar code label & rating plates. 2 mil adhesive recommended for application on textured surfaces.	UL, CSA
B-423	248 (10 min.)	White/Gloss	For electronic PCB & component; bar code label & rating plates.	UL, CSA, AGA

Chart Continued on Next Page