



Supplier	Product Description	Max Cooling Capacity (W)	LED Module Application	Diameter (mm)	Height (mm)	Thermal Resistance (°C/W)	Nuventix Part #***	Aavid Part #***
Aavid Thermalloy	Spotlight LED Heat Sink 34W - Flush Mount	22	Fortimo SLM, Vossloh-Schwabe	87	57	2.2	HSLCS-CALBL-020	070025
			Osram PrevaLED				HSLCS-CALBL-021	070026
			Configurable				HSLCS-CALBL-022	070027
			Bridgelux ES				HSLCS-CALBL-023	070109
			Xicato XSM				HSLCS-CALBL-024	-
			Zhaga B3				HSLCS-CALBL-025	070028
			LUXEON K				HSLCS-CALBL-027	070030
			Osram Soleriq, LEDiL				HSLCS-CALBL-028	070031
			Xicato XSM M3				HSLCS-CALBL-031	-
			Bridgelux Vero 13/18, ES, Molex Helieon				HSLCS-CALBL-034	070036
	Twist Module LED Heat Sink 43W	20	GE Infusion, Zhaga B5	100	42	2.4	NX300106	070109
	Spotlight LED Heat Sink 47W	26	Citizen, Bridgelux, Fortimo SLM, Zhaga B3	87	60	1.9	NX301101	070157
	Spotlight LED Heat Sink 38W	28	Configurable	100	57	1.8	HSLCS-CALBL-011	070017
			Fortimo SLM, Vossloh-Schwabe				HSLCS-CALBL-012	070018
			Osram PrevaLED				HSLCS-CALBL-015	070020
			Zhaga B3, Tridonic SLE				HSLCS-CALBL-019	070024
			Flush Xicato XSM M3				HSLCS-CALBL-030	070033
			Flush Bridgelux Vero 13/18, Molex Helieon				HSLCS-CALBL-035	070037
	Spotlight LED Heat Sink 60W	38	Configurable	118	42	1.3	NX300100	070105
			Fortimo SLM, Vossloh-Schwabe				NX300101	070106
			Osram PrevaLED				NX300102	070107
			Zhaga B3, Tridonic SLE, Philips SLM				NX300105	070108
			Xicato XSM				NX300128	070128
			Citizen CLL040, LEDiL				NX300150	070141
			Bridgelux RS, Vero 13/18/29				NX300158	070146
			GE Infusion, Zhaga B5				NX300131	070130

***Please contact marketing to confirm part numbers as they are transitioned from Nuventix to Aavid nomenclature