



**Your experts for
safety, facility
and equipment
identification**

Product Catalog

Indoor and Outdoor Vinyl Labels for Safety, Facility and Lean 5S (B-595)

Continuous vinyl material is ideal for lean 5S labels, pipe markers, equipment and production area identification. These labels offer excellent resistance to oils, detergents, dirt, grime and many solvents. Permanent adhesive, very pliable, good for rough surfaces and outdoor use. 8-10 years average outdoor durability.* Temp. range: -40° F to 180° F (-40° C to 82° C). UL recognized.



Figure 33



Figure	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Labels Per Roll	Rec. Ribbon
Fig. 33	M71C-250-595-WT	B-595	Vinyl	White	0.250 (6.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-500-595-WT	B-595	Vinyl	White	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-1000-595-WT	B-595	Vinyl	White	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-2000-595-WT	B-595	Vinyl	White	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-250-595-YL	B-595	Vinyl	Yellow	0.250 (6.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-500-595-YL	B-595	Vinyl	Yellow	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-1000-595-YL	B-595	Vinyl	Yellow	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-2000-595-YL	B-595	Vinyl	Yellow	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-500-595-BK	B-595	Vinyl	Black	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-1000-595-BK	B-595	Vinyl	Black	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-2000-595-BK	B-595	Vinyl	Black	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-500-595-BL	B-595	Vinyl	Blue	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-1000-595-BL	B-595	Vinyl	Blue	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-2000-595-BL	B-595	Vinyl	Blue	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-500-595-BR	B-595	Vinyl	Brown	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-1000-595-BR	B-595	Vinyl	Brown	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-2000-595-BR	B-595	Vinyl	Brown	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-500-595-CL	B-595	Vinyl	Clear	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-1000-595-CL	B-595	Vinyl	Clear	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-2000-595-CL	B-595	Vinyl	Clear	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-500-595-GD	B-595	Vinyl	Gold	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-1000-595-GD	B-595	Vinyl	Gold	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-2000-595-GD	B-595	Vinyl	Gold	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-500-595-GN	B-595	Vinyl	Green	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-1000-595-GN	B-595	Vinyl	Green	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-2000-595-GN	B-595	Vinyl	Green	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-500-595-GY	B-595	Vinyl	Gray	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-1000-595-GY	B-595	Vinyl	Gray	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-2000-595-GY	B-595	Vinyl	Gray	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-500-595-LB	B-595	Vinyl	Light Blue	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-1000-595-LB	B-595	Vinyl	Light Blue	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-2000-595-LB	B-595	Vinyl	Light Blue	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-500-595-OC	B-595	Vinyl	Ochre	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-1000-595-OC	B-595	Vinyl	Ochre	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-2000-595-OC	B-595	Vinyl	Ochre	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-500-595-OR	B-595	Vinyl	Orange	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-1000-595-OR	B-595	Vinyl	Orange	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-2000-595-OR	B-595	Vinyl	Orange	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-500-595-PK	B-595	Vinyl	Pink	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-1000-595-PK	B-595	Vinyl	Pink	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-2000-595-PK	B-595	Vinyl	Pink	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-500-595-PL	B-595	Vinyl	Purple	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-1000-595-PL	B-595	Vinyl	Purple	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-2000-595-PL	B-595	Vinyl	Purple	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-500-595-RD	B-595	Vinyl	Red	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-1000-595-RD	B-595	Vinyl	Red	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-2000-595-RD	B-595	Vinyl	Red	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71C-500-595-SB	B-595	Vinyl	Sky Blue	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-1000-595-SB	B-595	Vinyl	Sky Blue	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-2000-595-SB	B-595	Vinyl	Sky Blue	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-500-595-TN	B-595	Vinyl	Tan	0.500 (12.7)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-1000-595-TN	B-595	Vinyl	Tan	1.000 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71C-2000-595-TN	B-595	Vinyl	Tan	2.000 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000

* Average expected outdoor life of product will depend on user definition of failure, climatic conditions, mounting techniques and material color. The 8 to 10 year outdoor durability applies to the vinyl label stock only; ribbon durability will vary.

ToughWash® Harsh Washdown Labels (B-854 and B-855)

Specially formulated material for the Food and Beverage Processing industry with the ability to withstand washdowns up to 175° F (80° C) and pressure up to 1500 PSI.

- **B-854 ToughWash Metal Detectable Polyester:** Polyester material with aggressive adhesive. Capable of being detected by commercially available metal detectors
- **B-855 ToughWash Polyester:** Polyester material with aggressive acrylic adhesive




Figure 33




Figure 73



Figure	Catalog #	B#	Legend	Label Width A Inch (mm)	Length B Inch (mm)	Labels Per Roll	Rec. Ribbon
B-854 ToughWash® Metal Detectable Material							
Fig. 33	BM71C-1000-854-WT	B-854		1.000 (25.4)	75ft. (22.8 m)	1 roll (cont.)	M71-R6000
Fig. 33	BM71C-2000-854-WT	B-854		2.000 (50.8)	75ft. (22.8 m)	1 roll (cont.)	M71-R6000
Fig. 33	BM71C-1000-854-YL	B-854		1.000 (25.4)	75ft. (22.8 m)	1 roll (cont.)	M71-R6000
Fig. 33	BM71C-2000-854-YL	B-854		2.000 (50.8)	75ft. (22.8 m)	1 roll (cont.)	M71-R6000
Fig. 73	BM71C-2000-854-CAU	B-854		2.000 (50.8)	4.125 (104.8)	225	M71-R6000
Fig. 73	BM71C-2000-854-DAN	B-854		2.000 (50.8)	4.125 (104.8)	225	M71-R6000
Fig. 73	BM71C-2000-854-WAR	B-854		2.000 (50.8)	4.125 (104.8)	225	M71-R6000
B-855 ToughWash® Material							
Fig. 33	BM71C-1000-855-WT	B-855		1.000 (25.4)	75ft. (22.8 m)	1 roll (cont.)	M71-R6000
Fig. 33	BM71C-2000-855-WT	B-855		2.000 (50.8)	75ft. (22.8 m)	1 roll (cont.)	M71-R6000
Fig. 33	BM71C-1000-855-YL	B-855		1.000 (25.4)	75ft. (22.8 m)	1 roll (cont.)	M71-R6000
Fig. 33	BM71C-2000-855-YL	B-855		2.000 (50.8)	75ft. (22.8 m)	1 roll (cont.)	M71-R6000
Fig. 73	BM71C-2000-855-CAU	B-855		2.000 (50.8)	4.125 (104.8)	225	M71-R6000
Fig. 73	BM71C-2000-855-DAN	B-855		2.000 (50.8)	4.125 (104.8)	225	M71-R6000
Fig. 73	BM71C-2000-855-WAR	B-855		2.000 (50.8)	4.125 (104.8)	225	M71-R6000

ToughStripe® Floor Marking Labels (B-483)

Print on demand ToughStripe polyester floor marking material features the same durability and performance as ToughStripe tape with its high-adhesion to flat, non-coated concrete. Includes a roll of B-634 clear overlaminate to protect printing. Temp. range: -40° F to 248° F (-40° C to 120° C).




Figure 33



Figure	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Labels Per Roll	Rec. Ribbon
Fig. 33	M71-1000-483-WT-KT	B-483	Polyester	White	1.0 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71-2000-483-WT-KT	B-483	Polyester	White	2.0 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71-1000-483-YL-KT	B-483	Polyester	Yellow	1.0 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71-2000-483-YL-KT	B-483	Polyester	Yellow	2.0 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71-1000-483-BK-KT	B-483	Polyester	Black	1.0 (25.4)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71-2000-483-BK-KT	B-483	Polyester	Black	2.0 (50.8)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71-1000-483-BL-KT	B-483	Polyester	Blue	1.0 (25.4)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71-2000-483-BL-KT	B-483	Polyester	Blue	2.0 (50.8)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71-1000-483-GN-KT	B-483	Polyester	Green	1.0 (25.4)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71-2000-483-GN-KT	B-483	Polyester	Green	2.0 (50.8)	50 (15.2)	1 roll (cont.)	M71-R4400-WT
Fig. 33	M71-1000-483-OR-KT	B-483	Polyester	Orange	1.0 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71-2000-483-OR-KT	B-483	Polyester	Orange	2.0 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71-1000-483-RD-KT	B-483	Polyester	Red	1.0 (25.4)	50 (15.2)	1 roll (cont.)	M71-R6000
Fig. 33	M71-2000-483-RD-KT	B-483	Polyester	Red	2.0 (50.8)	50 (15.2)	1 roll (cont.)	M71-R6000