

Filament lamp, BA 9s base (MBC/MCC), 12 - 15 V**1.90.060.132/0000**

Ratings and operating life specifications generally refer to the lower rated voltage value.
Operating life specifications of lamps refer to AC operation. With DC operation, these are reduced by about 40%.

**Electrical characteristics**

Rated power	2 W
Rated voltage	12 - 15 V
Rated current	0.166 A

Other specifications

Diameter max.	11 mm
Length max.	29 mm
Medium operating life AC	10000 h
Socket	BA 9 s