

3 mm LED superbright red**1.90.690.269/0000****Electrical characteristics of LED**

Forward voltage typ. U_F at I_F	1.9 V/20 mA V
LED breakdown voltage U_R bei I_F	5 V/0.1 mA
Max. current, I_F	50 mA
Wavelength typ.	615 nm

Other specifications

Ambient temp. operating max.	+100 °C
Ambient temp. operating min.	-40 °C
Colour	red
Socket	without socket